



Multifunction voltage and frequency monitoring relays with NFC technology
PMV95N

Product designation

Product type designation

General characteristics

Description

Type of system

Three-phase with/without neutral

Power supply

Auxiliary supply voltage U_s	Self powered		
Operating voltage range	0.7...1.2 U_e		
Rated frequency	Hz		50/60 $\pm 5\%$
Power consumption Max	VA		30
Power dissipation Max	W		2.5

Control circuit

Rated voltage to control (U_e)	min	VAC	380
	Max	VAC	575

Voltage set-point ($\%U_e$)	min	%	80...95
	Max	%	105...115

Asymmetry set-point ($\%U_e$)	%		5...15
---------------------------------	---	--	--------

Frequency set-point ($\%$ rated frequency)	min	%	90...99
	Max	%	101...110

Tripping delay	s		0.1...30
----------------	---	--	----------

Resetting time	s		0.1...30
----------------	---	--	----------

Resetting hysteresis	%		1...5
----------------------	---	--	-------

Instantaneous tripping for U_e	Voltage $< 70\% U_e$		
----------------------------------	----------------------	--	--

Type of reset	Automatic or manual		
---------------	---------------------	--	--

Repeat accuracy	%		± 0.1
-----------------	---	--	-----------

Relay outputs

Number of relays	Nr.		1
------------------	-----	--	---

Relay state	Normally energised De-energises at tripping		
Contact arrangement	1 changeover SPDT		
Rated operational voltage AC (IEC)	VAC	250	
Maximum switching voltage	VAC	400	
IEC Conventional free air thermal current Ith	A	8	
UL/CSA and IEC/EN 60947-5-1 designation	B300		
Electrical life (with rated load)	cycles	100000	
Mechanical life	cycles	30000000	

Functions

Modular version	2U		
Minimum AC voltage	Yes		
Maximum AC voltage	Yes		
Natural loss	Yes		
Phase loss	Yes		
Incorrect phase sequence	Yes		
Asymmetry	Yes		
Minimum frequency	Yes		
Maximum frequency	Yes		
Programmable via NFC technology and APP	Yes		

Indications

Indication	1 green LED for power and 5 red LEDs for tripping		
------------	---	--	--

Connections

Terminals type	Screw		
Tightening torque for terminals	max	Nm	0.8
	max	Ibin	7
Conductor cross section			
AWG/Kcmil	min	AWG	24
	Max	AWG	12
IEC	min	mm ²	0.2
	Max	mm ²	4

Insulations

Rated insulation voltage Ui	V	600
Rated impulse withstand voltage Uimp	kV	6
Operating frequency withstand voltage	kV	4

Ambient conditions


Temperature			
Operating temperature	min	°C	-20
	max	°C	+60
Storage temperature	min	°C	-30
	max	°C	+80

Housing


Execution (n° of modules)	2		
---------------------------	---	--	--

Material	Self-extinguishing polyamide	
Mounting	35mm DIN rail (IEC/EN 60715)	
IEC degree of protection	IP40 on front; IP20 at terminals	
Dimensions (W x H x D)	mm	35.8 x 104.7 x 64.9
Weight	g	130

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°14

IEC/EN 60255-26

IEC/EN 60255-27

UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC001438 -
Voltage
monitoring relay