





Product designation	Single-phase energy meters		
Product type designation	DMED111MID		
Type	single-phase		
DIN rail module number	1		
Auxiliary supply U_s			
Operational frequency	min	Hz	50
Power consumption	Max	VA	7
Power dissipation Max		W	0.45
Measuring voltage inputs			
Rated voltage (U_e)	phase-neutral	VAC	230
Operating voltage range	phase-neutral	VAC	184...264
Connection method	Direct		
Current			
IEC maximum (I_{max})		A	40
IEC minimum (I_{min})		A	0.25
IEC rated (I_{ref-Ib})		A	5
IEC start (I_{st})		mA	20
Transition (I_{tr})		A	0.5
Accuracy			
	Active energy		Class B (EN 50470-3)
	Reactive energy		Class 2 (IEC/EN 62053-23)
RS485 serial interface			
Baud rate		bps	Programmable 1200...38400
Insulations			
Rated insulation voltage U_i IEC/EN		V	250
Rated impulse withstand voltage U_{imp}		kV	6
Operating frequency withstand voltage		kV	4
Mechanical features			
Housing type	Polyamide		
Terminals type	Fixed		
Conductor cross section	min	mm ²	1.5
	Max	mm ²	10
	min	AWG	16
	Max	AWG	6
Tightening torque (Max)		Nm	1.5

		lbin	14
Fixing			Din rail
Weight		g	90
Ambient conditions			
Temperature			
Operating temperature		min	°C -25
		max	°C +55
Storage temperature		min	°C -25
		max	°C +70
Relative humidity		%	<80
Maximum Pollution degree			2
Mechanical environment			Class M1
Magnetic environment			Class E2

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

EN50470-1

EN50470-3

TR 50579

Certificates

MID (modulo B + D)

RCM

ETIM classification

ETIM 8.0

EC001506 -
Kilowatt-hour
meter