



Product designation

Product type designation

Auxiliary supply voltage

Number of inputs

Number of outputs

Max I/O number

Micro PLC - Base  
module

LRD12RA024

24VAC

Nr. 8 digital

Nr. 4 relay

12 (8 inputs + 4  
outputs) up to 36  
with LRE  
modules

#### Power supply

Rated auxil. supply voltage		24VAC
Operating voltage range		20.4...28.8VAC
Rated frequency	Hz	50/60
Operating frequency range	Hz	47...63
Average current consumption	mA	290
Power consumption Max	W	7

#### Digital inputs

Number of digital input	Nr.	8
Rated voltage	V	24VAC (50/60Hz)
Input signals	State 0 (OFF) State 1 (ON)	<6VAC >14VAC

Response time

0 to 1 (OFF-ON)	90ms
1 to 0 (ON-OFF)	90ms

#### Digital outputs

Number of digital output	Nr.	4
type		Relay

#### System resources

Display	LCD display, 4 lines x 16 characters
---------	--

#### Connections

Terminals type	Screw
Tightening torque for terminals	max Nm 0.6 Max lbft 0.4

Conductor section

AWG/Kcmil

min	26
max	14

IEC

min	mm <sup>2</sup> 0.14
max	mm <sup>2</sup> 2.5

#### Ambient conditions

## Temperature

### Operating temperature

min	°C	-20
max	°C	+55

### Storage temperature

min	°C	-40
max	°C	+70

## Relative humidity

%	20...90% without condensation
---	-------------------------------

## Housing

## Mounting

35mm DIN rail or  
screw fixing  
(M4x20mm)

## Degree of protection

IP20


## Dimensions (W x H x D)

mm 72 x 106 x 59.6


## Weight

g 250

## Dimensions



## Wiring diagrams



## Certifications and compliance

### Compliance

CSA C22.2 n° 142

IEC/EN 61131-2

UL508

### Certificates

cULus

---

EAC

ETIM classification

ETIM 8.0

EC001417 -  
Logic module