



Product designation

Surge Protection
Device (SPD)

Product type designation

SA2E

Operating voltage type

DC

Application

DC Power lines

Number of DIN modules

3

Electrical features

Rated operational voltage DC	VDC	1100
Maximum continuous voltage Ucpv	V	1100
IEC Maximum discharge current I _{max} 8/20 (L-N/N-PE)	kA	40
IEC Rated discharge current (IEC) I _n 8/20 (L-N/N-PE)	kA	20
IEC Voltage protection level Up (L-N/N-PE)	kV	<4.0
Voltage protection level Up (L-L/L-PE)	kV	<4.0
Backup protection fuse (IEC) with I _{sc} >100A	Class/A	Not needed
IEC Maximum short circuit current at 50Hz	kA	50
Maximum short circuit current I _{scpv}	kA	9
Status indicator - operating / end of life		Frontal indication

Ambient conditions

Operating temperature

min	°C	-40
max	°C	+85


Max altitude

m	2000
---	------


Mechanical features

Fixing		Din rail
Conductor section Flexible max (IEC)	mm ²	25
Conductor section Rigid max (IEC)	mm ²	35
Cable stripping lenght	mm	15
Weight	g	329

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN/BS 50539-11

Certificates

EAC

ETIM classification

ETIM 8.0

EC000941 -
Surge protection
device for power
supply systems