



Key operated
KCN

Product designation

Product type designation

General characteristics

General characteristics

Housing Material

Polymer
thermoplastic

Key shape

Angled "T"

Contact characteristics

Type of contact

1NO+1NC Slow
action

Thermal current I_{th}

A 10

IEC/EN 60947-5-1 designation

A600 Q600

Rated insulation voltage U_i

V 690

Rated impulse withstand voltage U_{imp}

kV 6

Insulation class

II

Short-circuit protection with fuse

Class/A 10 gG/SC
QUICK FUSE

Switching speed

min	m/s	0.5
max	m/s	1.5

IEC Conventional free air thermal current I_{th}

A 10

Resistance per pole (average value)

mΩ <10

Operations

Mechanical life

cycles 100000

B10d

cycles 100000

Mechanical operation

cycles/h 3600

Output characteristics

Mechanical life

cycles 100000

Mechanical features

Operating head fixing

Locking bayonet
insert

Operating torque

N	8
I _b	1.8

Tightening torque (Max)

Switch fixing

Nm	2.5
I _{bin}	22.1

Contact terminals

Nm	0.8
I _{bin}	7

Body lid screw fixing

Nm	0.8
I _{bin}	7

Conductor section

AWG/Kcmil

min	16
max	14

IEC

min	mm ²	1or 2
max	mm ²	2.5

Cable connection

Self-releasing
screw terminal

Cable entry

M20 on the sides

Weight

g 107

Ambient conditions

Pollution degree

3

Temperature


Operating temperature

min	°C	-25
max	°C	+70

Storage temperature


min	°C	-40
max	°C	+70

Dimensions



Wiring diagrams

Slow action



1NO + 1NC

Certifications and compliance

Compliance

CSA C22.2 n° 14

EN 50047

IEC/EN 60204-1

IEC/EN 60947-1

IEC/EN 60947-5-1

UL508

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000030 - End
switch