



Interface
protection
system units
compliant with
italian standard
CEI 0-21
PMVF51

Product designation

Product type designation

General characteristics

Description

System with or
without neutral in
low voltage. Dual
threshold
minimum and
maximum voltage
and frequency
protection.

Type of system

Three-phase
with/without
neutral / Single-
phase

Power supply

Operating voltage range

85...264VAC /
93.5...300VDC

Rated frequency

Hz 45...55

Control circuit

Rated current (Ie)

A CT /5A /1A

Auxiliary supply

Rated auxiliary supply voltage Us

AC

min VAC 100
Max VAC 240

DC

min VDC 110
Max VDC 250

Power consumption

AC (Max)

VA 4.6VA at 110VAC;
12.5VA at
230VAC

DC (Max)

VA 23mA at
110VDC; 11mA
at 250VDC

Power dissipation

AC (Max)

	W	2.5W at 110VAC; 2.7W at 230VAC
DC (Max)		
	W	2.3W at 110VDC; 2.5W at 250VDC
Immunity time for microbreakings	ms	≤50ms at 100VDC; ≤200ms at 240VDC
Voltage inputs		
Maximum rated operational voltage		400VAC L-L; 230VAC L-N 50Hz
Measurement range	V	20...480VAC L-L; 10...276VAC L-N
Frequency range	Hz	45...55
Current inputs		
Measurement range		For 1A scale: 0.01...1.2A; for 5A scale: 0.01...6A
Measurement method		RMS
Overload peak	A	50A for 1 second
Burden per phase	W	≤0.6W
Relay outputs		
Number of relays	Nr.	2
Contact arrangement		1 changeover contact/SPDT each
Rated operational voltage AC (IEC)	VAC	250
UL/CSA and IEC/EN 60947-5-1 designation		For NO contact: 5A 250VAC AC1/C300; 5A 30VDC For NC contact: 2A 250VAC AC1/C300; 2A 30VDC
Digital inputs		
Number and type of inputs		4 negative (PNP)
Input voltage		12VDC isolated
Input current	mA	7
Connections		
Terminals type		Screw - removable
Tightening torque for terminals	max Nm	0.8
	max lbin	4.5
Conductor cross section		
AWG/Kcmil	min AWG	24
	Max AWG	12
IEC		


SCHNITTSTELLENSCHUTZGERÄT NACH ITALIENISCHEM STANDARD CEI 0-21 FÜR
EINPHASIGE UND DREIPHASIGE SYSTEME MIT ODER OHNE NEUTRAL IN
NIEDERSPANNUNG DOPPELSCHWELLENMINDEST- UND MAXIMALSPANNUNG UND
FREQUENZSCHUTZ 230VAC - 230VAC

min	mm ²	0.2
Max	mm ²	4


Housing

Execution (n° of modules)	6
Material	Polyamide
Mounting	Modular 6U
IEC degree of protection	IP40 on front; IP20 at terminals
Dimensions (W x H x D)	mm 108 x 105.4 x 63
Weight	g 470

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60255-5
IEC/EN 61000-6-2
IEC/EN 61000-6-3
IEC/EN 61010-1

Certificates

CEI 0-21

ETIM classification

ETIM 8.0

EC001438 -
Voltage
monitoring relay