



Product designation
Product type designation
Motor type

Soft Starter
ADX...B
Asynchronous
three phase

Electrical features

Supplies voltage

Type of system	Three phase
Rated supply voltage	208...500VAC
auxiliary supply voltage (Us)	208...240VAC
Rated frequency	50/60

Rated starter current Ie	A	110
--------------------------	---	-----

Rated motor power

IEC ratings (T≤40°C)

230VAC	kW	30
400VAC	kW	55
500VAC	KW	75

UL ratings (T≤40°C)

220-240VAC	HP	40
380-415VAC	HP	60
440-480VAC	HP	75

Number of controlled phases	Nr.	3
-----------------------------	-----	---

Built-in bypass	Yes
-----------------	-----

Cooling System	Forced
----------------	--------

Programming interface

Display	Backlit LCD 2x16 character
---------	----------------------------

Programming with NFC technology	No
---------------------------------	----

Optical port	No
--------------	----

Startup and stop settings

Startup method	Torque or voltage ramp with current limitation
----------------	--

Stop method	Torque ramp, voltage ramp, free-wheel stop
-------------	--

Braking method	DC dynamic with external relay
----------------	--------------------------------

Protections

Auxiliary supply protection	Voltage too low No power, phase loss, phase sequence, frequency out of limits, minimum and maximum voltage
Power supply Protection	

Motor protection

Overload at starting (trip class 2, 10A, 10, 15, 20, 25, 30, 35 and 40), overload during running (trip class 2, 10A, 10, 15, 20, 25 and 30), locked rotor, current asymmetry, minimum torque (dry run),

Starter protection

Overcurrent, overtemperature, bypass failure, phase shorted, temperature sensor fault, maintenance request

Functions

Built-in bypass	3
Built-in display and keypad	Yes
Languages	Yes
View measurements	4
Torque control	Yes
Adjustable current limit	Yes
Dynamic braking	Yes
Kick Start function	Yes
Motor overload electronic protection	Yes
Motor protection PTC input	Yes
Protection against phase loss	Yes
Protection against phase inversion	Yes
Protection against locked rotor	Yes
Protection against thyristor overtemperature	Yes
Protection against low load	Yes
Programmable alarm	Yes
Digital inputs	Yes
Analog inputs	Yes
Digital outputs	Yes
Analog output	Yes
Monitoring communication	Yes
Optical port for programming	RS323
Event log	No
Motor hour counter	Yes
Startup counter	Yes
Clock calendar	Yes
Remote external keypad	Yes
Plug-in version	Optional

Input and Output

Digital inputs

Number of digital input

Nr.

3 (2 digital inputs + 1 digital/analog input)

		Digital input type	24VDC (no need for external feeder)
		Digital input functions	1 input for start, 1 input programmable (stop, free-wheel stopping, external alarm, motor preheat, local control, alarms inhibit, manual resetting of motor thermal protection, keypad lock, second moto
Analog inputs			
		Number of analog input	Nr. 1 (digital/analog)
		Analog input type	0-10VDC (0-20mA with external resistor 500Ω)
		Analog input functions	Motor protection via PTC probes, acceleration and/or deceleration ramp via analog input, analog input thresholds for motor starting and stopping, analog input thresholds for programmable relay enable
Digital outputs			
		Number of digital output	Nr. 4
		Digital output arrangement	3 x 1 NO (SPST) + 1 C/O (SPDT) Ratings: 5A 250VAC AC1, 2A 250VAC AC15 C/O output for global alarm, 3 x 1NO outputs programmable (OFF, motor powered, up to speed, braking, current limit, service required, cascade starting, programmable input thresholds, alarm Axx)
		Digital output functions	
Analog outputs			

Number of analog output	Nr.	1
Analog output type		0...20mA, 4...20mA (0...10V with external resistor 500Ω)
Analog output functions		Current, torque, motor thermal status, power factor and active power

Ambient conditions

Temperature

Operating temperature

min	°C	-10
max	°C	+55°C (with current derating >45°C of 1.5%/ °C)

Storage temperature

min	°C	-30
max	°C	+70

Max altitude

m	1000 without derating (over 1000mt with current derating of 0.5%/100m)
---	--

Relative humidity

%	95% without condensation or dripping
---	--

Pollution degree

3

Housing

Mounting

Screw-fixing

IP degree of protection

IP20


Dimensions (W x H x D)

mm 157 x 584 x 250

Weight

Kg 17.7

Dimensions



TYPE	A	B	C	D	E
ADX 0017B	157 (6.18")	372 (14.64")	223 (8.78")	131 (5.16")	357 (14.05")
ADX 0030B	157 (6.18")	372 (14.64")	223 (8.78")	131 (5.16")	357 (14.05")
ADX 0045B	157 (6.18")	372 (14.64")	223 (8.78")	131 (5.16")	357 (14.05")
ADX 0060B	157 (6.18")	534 (21.02")	250 (9.84")	132 (5.20")	517 (20.35")
ADX 0075B	157 (6.18")	534 (21.02")	250 (9.84")	132 (5.20")	517 (20.35")
ADX 0085B	157 (6.18")	534 (21.02")	250 (9.84")	132 (5.20")	517 (20.35")
ADX 0110B	157 (6.18")	584 (22.99")	250 (9.84")	132 (5.20")	567 (22.32")
ADX 0125B	157 (6.18")	584 (22.99")	250 (9.84")	132 (5.20")	567 (22.32")

Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-2

Certificates

CCC
EAC

ETIM classification

ETIM 8.0

EC000640 - Soft
starter