




Product designation				Modular switching power supplies	
Product type designation				PSL1M	
Input characteristics					
Input type				Single-phase	
Rated supply voltage AC				VAC	Multivoltage 100...240
Operating range					
AC		min	VAC	90	
		Max	VAC	264	
DC		min	VDC	120	
		Max	VDC	375	
Rated frequency				Hz	50/60
Operational frequency				min	Hz 47
				max	Hz 63
Current consumption Max				mA	300
PFC				No	
Insulation voltage Input/Output				AC	VAC 3000
				DC	VAC 4242
Internal fuse (250VAC)				T1A 250VAC	
Output characteristics					
Rated output voltage DC				VDC	12
Rated output current				A	0.83
Rated output power				W	10
Temperature coefficient				%/°C	±0.03
Line adjustment				%	±1
Load adjustment				%	±1
Efficiency				%	79
Overload protection				125...185%	
Short-circuit protection				Hiccup	
Ripple & noise				mV	50
Parallel connection				Nr.	No
Indications					
LED indicator for power on				Yes	
LED indicator for low voltage				Yes	
Connections					
Terminals type				Screw	
Ambient conditions					
Temperature					
Operating temperature		min	°C	-40	

Storage temperature	max	°C	+71
	min	°C	-40
	max	°C	+85
Derating		%/°C	2.5%/°C above 60°C


Housing			
Execution (n° of modules)			1
Material			Plastic
IEC degree of protection			IP20
Dimensions (W x H x D)	mm		18 x 96 x 56.2
Weight	g		114

Installations			
Mounting			On 35mm DIN rail

Dimensions			
-------------------	--	--	--



Wiring diagrams			
------------------------	--	--	--



Certifications and compliance			
--------------------------------------	--	--	--

Compliance	CSA C22.2 n°14		
	IEC/EN/BS 61000-6-2		
	IEC/EN/BS 61000-6-3		

IEC/EN/BS 62368-1

UL 508

Certificates

cULus

EAC

RCM

ETIM classification

ETIM 8.0

EC002540 - DC-
power supply