



Product designation  
Product type designation

Remote units  
RGKRA

#### Power supply

Rated battery voltage

V 100/240VAC -  
12/24VDC

#### Static Outputs

Static output type

(SSR)

#### Interface

CANbus

Yes

#### Mechanical features

Conductor cross section

|     |                 |                 |
|-----|-----------------|-----------------|
| min | mm <sup>2</sup> | 0.2             |
| Max | mm <sup>2</sup> | 2.5             |
| min | AWG             | 24 or 18 UL/CSA |
| Max | AWG             | 12              |

Tightening torque (Max)


Nm 0.56  
lbin 4.5

#### Ambient conditions


Protection degree

IP54

#### Dimensions



#### Wiring diagrams



## Certifications and compliance

### Compliance

CSA C22.2 n° 14

IEC 61000-6-3

IEC/EN 61000-6-2

IEC/EN 61010-1

UL508

### Certificates

EAC

UL Listed for USA and Canada (cULus-File E93601)

## ETIM classification

ETIM 8.0

EC001427 -  
Mobile panel