



Product designation

Product type designation

Type

DIN rail module number

Three-phase
energy meters
DMED300T2
Three-phase +
neutral
4

Auxiliary supply U_s

Operational frequency

min	Hz	50
max	Hz	60

Power consumption

Max	VA	20
-----	----	----

Power dissipation Max

W	1.35
---	------

Measuring voltage inputs

Rated voltage (U_e)

phase-phase	VAC	380...415
phase-neutral	VAC	220...240

Operating voltage range

phase-phase	VAC	323...456
phase-neutral	VAC	187...264

Connection method

Direct

Current

IEC maximum (I_{max})

A	80
---	----

IEC minimum (I_{min})

A	0.5
---	-----

IEC rated (I_{ref-Ib})

A	10
---	----

IEC start (I_{st})

mA	60
----	----

Transition (I_{tr})

A	1
---	---

Accuracy

Active energy	Class 1 (IEC/EN 62053-21)
Reactive energy	Class 2 (IEC/EN 62053-23)

Output characteristics

LED Pulse rate

pulse/kWh	1000
-----------	------

LED Pulse duration

ms	30
----	----

Static output pulse rate

pulse/kWh	1-10-100-1000 programmable
-----------	-------------------------------

Static output pulse duration

ms	100 for 1-10-10 pulse; 60 for 1000 pulse
----	--

Static output external voltage

VDC	10...30
-----	---------

Static outputs Maximum current

mA	50
----	----

Insulations

Rated insulation voltage U_i IEC/EN

V	250
---	-----

Rated impulse withstand voltage U_{imp}

kV	6
----	---

Operating frequency withstand voltage

kV	4
----	---


Mechanical features

Housing type	Polyamide		
Terminals type	Fixed		
Conductor cross section	min	mm ²	2.5
	Max	mm ²	25
	min	AWG	14
	Max	AWG	4
Tightening torque (Max)		Nm	2
		lbin	17.7
Fixing	Din rail		
Weight		g	360


Ambient conditions

Temperature	Operating temperature		
	min	°C	-25
	max	°C	+55
	Storage temperature		
	min	°C	-25
	max	°C	+70
Relative humidity			%
			<80
Maximum Pollution degree			2

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 50470-1

IEC/EN 61010-1

IEC/EN 61010-2-030

Certificates

EAC

RCM

ETIM classification

ETIM 8.0

EC001506 -
Kilowatt-hour
meter