



Product designation

Product type designation

Type

DIN rail module number

Three-phase
energy meters
DMED300T2MID
Three-phase +
neutral
4

Auxiliary supply U_s

Operational frequency

min Hz 50

Power consumption

Max VA 20

Power dissipation Max

W 1.35

Measuring voltage inputs

Rated voltage (U_e)

phase-phase VAC 400
phase-neutral VAC 230

Operating voltage range

phase-phase VAC 323...456
phase-neutral VAC 187...264

Connection method

Direct

Current

IEC maximum (I_{max})

A 80

IEC minimum (I_{min})

A 0.5

IEC rated (I_{ref-Ib})

A 10

IEC start (I_{st})

mA 40

Transition (I_{tr})

A 1

Accuracy

Active energy Class B (EN 50470-3)
Reactive energy Class 2 (IEC/EN 62053-23)

Output characteristics

LED Pulse rate

pulse/kWh 1000

LED Pulse duration

ms 30

Static output pulse rate

pulse/kWh 1-10-100-1000
programmable

Static output pulse duration

ms 100 for 1-10-10
pulse; 60 for
1000 pulse

Static output external voltage

VDC 10...30

Static outputs Maximum current

mA 50

Insulations

Rated insulation voltage U_i IEC/EN

V 250

Rated impulse withstand voltage U_{imp}

kV 6


Operating frequency withstand voltage

kV 4


Mechanical features

Housing type			Polyamide		
Terminals type			Fixed		
Conductor cross section			min	mm²	2.5
			Max	mm²	25
			min	AWG	14
			Max	AWG	4
Tightening torque (Max)			Nm	2	
			lbin	17.7	
Fixing			Din rail		
Weight			g	360	
Ambient conditions					
Temperature					
Operating temperature		min	°C	-25	
		max	°C	+55	
Storage temperature		min	°C	-25	
		max	°C	+70	
Relative humidity			%	<80	
Maximum Pollution degree			2		
Mechanical environment			Class M1		
Magnetic environment			Class E2		

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

EN50470-1

EN50470-3

TR 50579

Certificates

EAC

MID (moduli B + D)

RCM

ETIM classification

ETIM 8.0

EC001506 -
Kilowatt-hour
meter