



Product designation

Switch
disconnecter

Product type designation

GA

Number of poles

Nr.

3

Operating voltage type

AC

Contact characteristics

IEC Conventional free air thermal current I _{th}	A	32
---	---	----

Rated insulation voltage U _i IEC/EN	V	1000
--	---	------

Rated impulse withstand voltage U _{imp}	kV	8
--	----	---

Operating current I_e

AC21A

400V	A	32
500V	A	32
690V	A	32

AC22A

400V	A	32
500V	A	32
690V	A	32

AC23A

400V	A	32
500V	A	25
690V	A	25

Power dissipation per pole max	W	0.6
--------------------------------	---	-----

Rated operational power AC23A

400V	kW	15
690V	kW	22

Rated short time current (1s) I _{cw} (rms)	kA	0.8
---	----	-----

Conditional short-circuit current (rms)	kA	10
---	----	----

Short-circuit protection with fuse	Class/A	gG32
------------------------------------	---------	------

Making capacity AC23A 400V	A	400
----------------------------	---	-----

Breaking capacity AC23A 400V	A	320
------------------------------	---	-----

Mechanical life	cycles	100000
-----------------	--------	--------

Electrical life AC21A	cycles	100000
-----------------------	--------	--------

Mechanical features

Operating position

normal
allowable

Vertical plan
Any

Fixing

Screw / DIN rail
35mm

Terminals

type	Pillar
width	5.6
height	6.5
screw	M4
tool	Phillips 2

Tightening torque for terminals

min	Nm	1.8
max	Nm	2
min	lbin	16
max	lbin	18

Conductor section

IEC min	mm ²	0.75
IEC max	mm ²	16
AWG/kcmil min		18
AWG/kcmil max		6

Ambient conditions

Operating temperature

min	°C	-25
max	°C	55

Storage temperature

min	°C	-40
max	°C	70

Max altitude

m	3000
---	------

Resistance & Protection


Frontal IP degree

IP20


Pollution degree

3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°60947-4-1

IEC/EN 60947-1

IEC/EN 60947-3

UL60947-4-1

Certifications

CCC

CSA C22.2 n°60947-4-1

cULus according to UL60947-4-1

EAC

KEMA

ETIM classification

ETIM 8.0

EC000216 -
 Switch
 disconnecter