





Product designation			LED integrated monoblock pilot lights steady light LPML	
Product type designation				
General characteristics				
Colour			Red	
Type of positions			Monoblock pilot light	
Material			Polyamide	
IEC degree of protection			IP66, IP67 and IP69K on front; IP20 on rear	
Electrical characteristics				
Rated frequency		Hz	50-60	
Supply voltage (AC)		V	230 (-15% ... +10% Ue)	
Operations				
Electrical life		hours	>30000	
Mechanical features				
Tightening torque for terminals max		Nm	0.8	
Terminals screw			Screw termination	
Conductor section				
		AWG/kcmil conductor section		
		min	18	
		max	16	
		IEC		
		max	mm²	2.5
Fixing			Ring fixing Ø22mm	
Weight			g	24
UL technical data				
UL degree of protection			Type1, 2, 3R, 4, 4X, 12, 12K on front	
Ambient conditions				
Temperature				
		Operating temperature		
		min	°C	-25
		max	°C	+70
Dimensions				



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000272 -
Indicator light
complete