



Product designation Power contactor  
Product type designation B630

### Contact characteristics

Number of poles	Nr.	4
Rated insulation voltage $U_i$ IEC/EN	V	1000
Rated impulse withstand voltage $U_{imp}$	kV	8
Operational frequency	min Hz	25
	max Hz	400
IEC Conventional free air thermal current $I_{th}$	A	800
Operational current $I_e$		
	AC-1 ( $\leq 40^\circ\text{C}$ )	A 800
	AC-1 ( $\leq 55^\circ\text{C}$ )	A 640
	AC-1 ( $\leq 70^\circ\text{C}$ )	A 540
	AC-3 ( $\leq 440\text{V} \leq 55^\circ\text{C}$ )	A 630
	AC-4 (400V)	A 260
Rated operational power AC-1 ( $T \leq 40^\circ\text{C}$ )		
	230V kW	288
	400V kW	500
	500V kW	655
	690V kW	860
IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 1 poles in series		
	75V A	800
	110V A	460
	220V A	--
	330V A	--
	460V A	--
IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 2 poles in series		
	75V A	800
	110V A	800
	220V A	700
	330V A	--
	460V A	--
IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 3 poles in series		
	75V A	800
	110V A	800
	220V A	800
	330V A	700
	460V A	--
IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 4 poles in series		
	75V A	800
	110V A	800
	220V A	800
	330V A	750
	460V A	700

IEC max current  $I_e$  in DC3-DC5 with  $L/R \leq 15\text{ms}$  with 1 poles in series

75V	A	800
110V	A	460
220V	A	--
330V	A	--
460V	A	--

IEC max current  $I_e$  in DC3-DC5 with  $L/R \leq 15\text{ms}$  with 2 poles in series

75V	A	800
110V	A	800
220V	A	700
330V	A	--
460V	A	--

IEC max current  $I_e$  in DC3-DC5 with  $L/R \leq 15\text{ms}$  with 3 poles in series

75V	A	800
110V	A	800
220V	A	800
330V	A	650
460V	A	--

IEC max current  $I_e$  in DC3-DC5 with  $L/R \leq 15\text{ms}$  with 4 poles in series

75V	A	800
110V	A	800
220V	A	800
330V	A	650
460V	A	700

Short-time allowable current for 10s (IEC/EN60947-1)

A	5040
---	------

Protection fuse

gG (IEC)	A	1000
aM (IEC)	A	630

Making capacity (RMS value)

A	6300
---	------

Breaking capacity at voltage

440V	A	6300
500V	A	5600
690V	A	5000

Resistance per pole (average value)

mΩ	0.14
----	------

Power dissipation per pole (average value)

$I_{th}$	W	90
AC-3	W	56

Tightening torque for terminals

min	Nm	55
max	Nm	55
min	Ibin	40.6
max	Ibin	40.6

Tightening torque for coil terminal

min	Nm	1
max	Nm	1
min	Ibin	0.74
max	Ibin	0.74

Max number of wires simultaneously connectable

Nr.	2
-----	---

Conductor section

AWG/Kcmil

max	2x 600 kcmil
-----	--------------

Power terminal protection according to IEC/EN 60529

IP00

**Mechanical features**

## Operating position

	normal allowable	Vertical plan ±30°
Fixing		Screw
Weight	g	2194

## Conductor section

AWG/kcmil conductor section

max

2x 600 kcmil

## Operations

Mechanical life	cycles	5000000
Electrical life	cycles	700000

## Safety related data

Performance level B10d according to EN/ISO 13489-1

	rated load mechanical load	cycles	700000
		cycles	5000000
Mirror contacts according to IEC/EN 60947-4-1			yes
EMC compatibility			yes

## AC coil operating

Rated AC voltage at 50/60Hz, 60Hz

min	V	220
max	V	240

## AC operating voltage

of 50/60Hz coil powered at 50Hz  
pick-up

min	%Us	80
max	%Us	110

drop-out

min	%Us	20
max	%Us	60

of 50/60Hz coil powered at 60Hz  
pick-up

min	%Us	80
max	%Us	110

drop-out

min	%Us	20
max	%Us	60

of 60Hz coil powered at 60Hz  
pick-up

min	%Us	80
max	%Us	110

drop-out

min	%Us	20
max	%Us	60

## AC average coil consumption at 20°C

of 50/60Hz coil powered at 50Hz

in-rush	VA	400
holding	VA	18

of 50/60Hz coil powered at 60Hz

in-rush	VA	400
holding	VA	18


## Dissipation at holding ≤20°C 50Hz

W	18
---	----

## DC coil operating


DC rated control voltage

		min	V	220	
		max	V	240	
DC operating voltage					
pick-up					
		min	%Us	80	
		max	%Us	110	
drop-out					
		min	%Us	20	
		max	%Us	60	
Average coil consumption ≤20°C					
		in-rush	W	400	
		holding	W	18	
Max cycles frequency					
Mechanical operation			cycles/h	1200	
Operating times					
Average time for Us control					
in AC	Closing NO				
		min	ms	110	
		max	ms	180	
	Opening NO				
		min	ms	60	
		max	ms	100	
	in DC	Closing NO			
			min	ms	110
			max	ms	180
Opening NO					
		min	ms	60	
		max	ms	100	
UL technical data					
General USE					
Contactor					
	AC current	A	800		
Short-circuit protection fuse, 600V					
Standard fault					
	Short circuit current	kA	18		
	Fuse rating	A	1500		
	Fuse class		L		
Ambient conditions					
Temperature					
Operating temperature					
		min	°C	-50	
		max	°C	70	
	Storage temperature				
		min	°C	-60	
max		°C	80		
Max altitude			m	3000	
Resistance & Protection					
Pollution degree				3	
Dimensions					



CONTACTOR TYPE	A	B	C
B500	M10	35 (1.38")	265 (10.43")
B630	M12	40 (1.57")	270 (10.63")

## Wiring diagrams



## Certifications and compliance

### Compliance

CSA C22.2 n° 60947-1  
CSA C22.2 n° 60947-4-1  
IEC/EN 60947-1  
IEC/EN 60947-4-1  
UL 60947-1  
UL 60947-4-1

### Certificates

CCC  
cULus  
EAC

## ETIM classification

ETIM 8.0

EC000066 -  
Power contactor,  
AC switching