



Product designation
Product type designation
Motor type

Soft Starter
ADXL
Asynchronous
three phase

Electrical features

Supplies voltage

Type of system	Three phase
Rated supply voltage	208...600VAC
auxiliary supply voltage (Us)	100...240VAC
Rated frequency	50/60

Rated starter current Ie	A	30
--------------------------	---	----

Rated motor power

IEC ratings (T≤40°C)

230VAC	kW	7.5
400VAC	kW	15
500VAC	KW	18.5

UL ratings (T≤40°C)

220-240VAC	HP	10
380-415VAC	HP	15
440-480VAC	HP	20
550-600VAC	HP	25

Number of controlled phases	Nr.	2
-----------------------------	-----	---

Built-in bypass	Yes
-----------------	-----

Cooling System	Natural or forced (optional)
----------------	------------------------------

Rated insulation voltage Ui	V	600
-----------------------------	---	-----

Programming interface

Display	Backlit icon LCD display
---------	--------------------------

Programming with NFC technology	Yes
---------------------------------	-----

Optical port	Yes
--------------	-----

Startup and stop settings

Startup method	Torque ramp with current limit, Voltage ramp with current limit, Constant torque with current limit
----------------	---

Stop method	Torque ramp, voltage ramp, free-wheel stop
-------------	--

Protections

Auxiliary supply protection	Voltage too low
-----------------------------	-----------------

Power supply Protection	No power, phase loss, phase sequence, frequency out of limits, minimum and maximum voltage
Motor protection	Overload at starting (trip class 2, 10A, 10, 15, 20, 25, 30, 35 and 40), overload during running (trip class 2, 10A, 10, 15, 20, 25 and 30), locked rotor, current asymmetry, minimum torque (dry run),
Starter protection	Overcurrent, overtemperature, bypass failure, phase shorted, temperature sensor fault, cooling fan fault, maintenance request

Functions	
Built-in bypass	2
Built-in display and keypad	Yes
Languages	Yes
View measurements	6
Torque control	Yes
Adjustable current limit	Yes
Dynamic braking	Yes
Kick Start function	No
Motor overload electronic protection	Yes
Motor protection PTC input	Yes
Protection against phase loss	Yes
Protection against phase inversion	Yes
Protection against locked rotor	Yes
Protection against thyristor overtemperature	Yes
Protection against low load	Yes
Programmable alarm	Yes
Digital inputs	Yes
Analog inputs	Yes
Digital outputs	No
Analog output	Yes
Monitoring communication	No
Optical port for programming	RS485
Event log	Yes
Motor hour counter	Yes
Startup counter	Yes

Clock calendar	Yes
Remote external keypad	No
Plug-in version	Optional

Input and Output

Digital inputs				
	Number of digital input	Nr.	3	
	Digital input type		2 input with dry contact + 1 input with dry contact or PTC (configurable)	
	Digital input functions		Programmable (motor start, motor stop, freewheel stop, motor preheating, commands lock, alarms inhibition, thermal status reset, keyboard lock, motor selection, user alarm, command)	


Digital outputs				
	Number of digital output	Nr.	3	
	Digital output arrangement		2 x 1 NO (SPST) + 1 C/O (SPDT) Ratings: 2 x 1NO contacts: 3A 250VAC - 3A 30VDC 1 x C/O contact: NO contact 5A 250VAC - 5A 30VDC; NC contact 3A 250VAC - 3A 30VDC	
	Digital output functions		Programmable (line contactor, run, global alarm, limits, remote variable, alarm Axx, user alarm Axx, OFF)	

Ambient conditions

Temperature				
	Operating temperature			
		min	°C	-20
		max	°C	+60°C (with current derating >40°C of 0.5%/°C)
	Storage temperature			
		min	°C	-30
		max	°C	+80

Max altitude	m	1000 without derating (over 1000mt with current derating of 0.5%/100m)
Relative humidity	%	<80%
Pollution degree		2
Installation category		III
Housing		
Mounting		Screw-fixing or 35mm DIN rail with optional accessory EXP8003
IP degree of protection		IP00
Dimensions (W x H x D)	mm	75 x 218 x 171.5
Weight	Kg	2.1

Dimensions



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN 60947-1
IEC/EN 60947-4-2

SOFT STARTER, ADXL... TYPE, WITH INTEGRATED BY-PASS RELAY. AUXILIARY SUPPLY
100...240VAC. RATED OPERATIONAL VOLTAGE 208...600VAC, 30A

UL508

Certificates

cULus

EAC

RCM

ETIM classification

ETIM 8.0

EC000640 - Soft
starter