





Product designation			Variable speed drives
Product type designation			VLA1
General characteristics			
Rated power supply voltage			200...240VAC 50/60Hz
Rated output voltage		VAC	Three-phase 0...240VAC 0-599Hz
Rated output current		A	7
Rated output power		kW	1.5
Rated output power		HP	2
EMC filter			Built-in EMC suppressor cat. C2
Communication port			None
Technical features			
Input type			Single-phase
Rated mains voltage		VAC	200...240
Operating mains voltage range		VAC	170...264
Rated mains frequency		Hz	50/60
Operating mains frequency range		Hz	45...65
Rated mains current without mains choke			16.7
Rated mains current with mains choke			13.9
Output type			Three-phase
Output voltage range		VAC	0...240
Output frequency range		Hz	0...599
Current overload		%/s	150% for 60s, 200% for 3s
Power loss			50W
Brake chopper			No
Switching frequency			2...16kHz
Max motor cable length			
Shielded			
		Without EMC category	m 50
		Category C2	m 20
Functions			
Motor control modes			

Speed reference signals	External potentiometer 0...10kΩ Voltage signals: 0...10VDC Current signals: 0/4...20mA Buttons on front keyboard Door-mount installation kit 15 preset speeds via digital inputs Motor potentiometer	
	3-wire control	Yes
	S-shape curves	Yes
	Slip compensation	Yes
	Flying restart	Yes
	Access to DC bus	No
	DC braking	Yes
	DC injection at start	Yes
	PID control	Yes, with sleep and rinse function
	Sequencer (programmable frequency/time cycles)	Yes
	Preset speeds	Yes
	Motorpotentiometer	Yes
	Different parameter configuration sets	Yes
	Parameters changeover function	Yes
	Favorite parameters menu	Yes
Autotuning	No	
Safe torque Off (STO) safety function	No	
PTC probe input	No	
Protections	Overcurrent Output short circuit and earth/ground leakage Overvoltage Undervoltage Phase loss Motor heat overload (i2t) Overspeed Speed reverse	
	Multi-pump PID control (1 main pump frequency regulated + 2 auxiliary pumps activated in direct mode in case of necessity)	
Special funct.		
Input and Output		
Number of digital input	Nr.	5
Digital input type		Selectable PNP or NPN logic
Number of digital output	Nr.	2

Digital output arrangement					1 relay output with changeover contact (C/O-SPDT) + 1 digital output
Output contacts ratings					Relay output: 3A 250VAC Digital output: 100mA max 30VDC
Number of analog input		Nr.			2
Analog input type					Analog input 1: configurable 0/2...10VDC, 0...5VDC, 0/4...20mA Analog input 2: configurable 0/2...10VDC or 0...5VDC
Number of analog output		Nr.			1
Analog output type					configurable as 0...10VDC, 0...5VDC, 2...10VDC, 0/4...20mA
Ambient conditions					
Temperature					
	Operating temperature				
		min	°C		-10
		max	°C		+55
		Current derating			2.5%/°C over 40°C
	Storage temperature				
		min	°C		-25
		max	°C		+60
Relative humidity			%		5...95% (with no condensing)
Max altitude			m		4000m (over 1000m derate the rated current by 5%/1000m)
Maximum Pollution degree					2
Overvoltage category					III up to 2000m altitude (II above 2000m)
Housing					
Installation position					Vertical
IP degree of protection					IP20
Dimensions (W x H x D)			mm		60 x 281 x 130
Weight			Kg		1.35
Dimensions					



Wiring diagrams



Certifications and compliance

Compliance

CSA 22.2 No. 274

EN 61800-5-1

UL61800-5-1

Certificates

cULus

EAC

RCM

ETIM classification

ETIM 8.0

EC001857 -
Frequency
converter =< 1 kW