



Panel m. color
glcd mult.,
Ethernet
DMG8000
Three-phase +
neutral

Product designation

Product type designation

Type

Auxiliary supply Us

Auxiliary rated supply voltage AC	VAC	100...240
Auxiliary rated supply voltage DC	VDC	110...250
Auxiliary operating voltage range		
AC	min	VAC 90
	Max	VAC 264
DC	min	VDC 100
	Max	VDC 300

Operational frequency	min	Hz	45
	max	Hz	66

Power consumption	Max	VA	15
Power dissipation Max		W	6

Measuring voltage inputs

Rated voltage (Ue)	phase-phase	VAC	600
	phase-neutral	VAC	347

Operating voltage range	phase-phase	VAC	40...830
	phase-neutral	VAC	5...480

Voltage inputs operational frequency	min	Hz	45 and 360
	max	Hz	66 and 440

Voltage inputs measurement method			True RMS
-----------------------------------	--	--	----------

Connection method			Single. Two. Three-phase with or without neutral. Balanced three- phase system. Three-phase ARON.
-------------------	--	--	---

Current inputs

Rated current (Ie)	A	1A/5A
Measurement range		0.004...6
Measurement method		TRMS


ANALIZADOR DE RED CON AMPLIA PANTALLA LCD A COLOR. ALIMENTACIÓN AUXILIAR 100...240VAC. EXPANDIBLE CON 3 MÓDULOS EXP... , PUERTO DE COMUNICACIÓN ETHERNET INCORPORADO, MEMORIA DE DATOS PARA EL REGISTRO, COMPATIBLE CON EL SISTEMA DE MEDIDA MULTICIRCUITO EASY BRANCH

Overload capacity			+20% I _e by external CT with 5A secondary
Overload peak	A		120A for 0.5s
Accuracy			
			Class 0.2 (IEC/EN 61557-12), V:50-480V~
	VLN voltage		Class 0.2 (IEC/EN 61557-12), V:87-830V~
	VLL voltage		Class 0.2 (IEC/EN 61557-12), I _n :5A~
	Current		Class 0.02 (IEC/EN 61557-12)
	Frequency		Class 0.5 (IEC/EN 61557-12)
	Active power		Class 1 (IEC/EN 61557-12)
	Reactive power		Class 0.5s (IEC/EN 62053-22)
	Active energy		Class 1 (IEC/EN 62053-24)
	Reactive energy		Class 5 (IEC/EN 61557-12)
	THD		Class 5 (IEC/EN 61557-12)
	2nd 15th order harmonics		Class 5 (IEC/EN 61557-12)
Insulations			
Rated insulation voltage U _i IEC/EN	V		600
Rated impulse withstand voltage U _{imp}	kV		9.6
Operating frequency withstand voltage	kV		5.4
Functions			
Harmonic analysis			63rd order
PLC logic			Yes
Type of communication port			Ethernet
Ethernet-RS485 gateway function			+EXP1012
Data logging memory			Yes
Neutral/earth current and voltage monitoring			No
Statistics of network quality according to EN50160			No
EASY BRANCH support			Yes
Mechanical features			
Housing type			Xantar RAL 7035
Terminals type			Removable
Conductor cross section			
	min	mm ²	0.2
	Max	mm ²	2.5
	min	AWG	24
	Max	AWG	12
Tightening torque (Max)			
		Nm	0.5
		lbin	4.5

ANALIZADOR DE RED CON AMPLIA PANTALLA LCD A COLOR. ALIMENTACIÓN AUXILIAR 100...240VAC. EXPANDIBLE CON 3 MÓDULOS EXP..., PUERTO DE COMUNICACIÓN ETHERNET INCORPORADO, MEMORIA DE DATOS PARA EL REGISTRO, COMPATIBLE CON EL SISTEMA DE MEDIDA MULTICIRCUITO EASY BRANCH

Fixing	Flush-mounting		
Weight	g	420	
Ambient conditions			
Temperature			
Operating temperature	min	°C	-20
	max	°C	+60
Storage temperature	min	°C	-30
	max	°C	+80
Relative humidity			% <80
Maximum Pollution degree			2
Protection degree			IP65


Dimensions




① Dimensions with gasket: 122x100mm/4.80x3.94".

Wiring diagrams


Single-phase





Two-phase




Three-phase with or without neutral



Three-phase without neutral in ARON connection



Balanced 3-phase connection with or without neutral



CODE	AUX SUPPLY
DMG100-110-200-210-300	100...240VAC 110...250VDC
DMG6...	100...440VAC 110...250VDC
DMG7000-7500-8000-9000	100...240VAC 110...250VDC

RS485 for DMG110 and DMG210



RS485 for DMG610



RS485 for DMG7500 and DMG9000



Certifications and compliance

Compliance

IEC/EN/BS 61000-6-2

IEC/EN/BS 61000-6-4

ANALIZADOR DE RED CON AMPLIA PANTALLA LCD A COLOR. ALIMENTACIÓN AUXILIAR 100...240VAC. EXPANDIBLE CON 3 MÓDULOS EXP... , PUERTO DE COMUNICACIÓN ETHERNET INCORPORADO, MEMORIA DE DATOS PARA EL REGISTRO, COMPATIBLE CON EL SISTEMA DE MEDIDA MULTICIRCUITO EASY BRANCH

IEC/EN/BS 61010-1

Certificates

CE

EAC

UKCA

ETIM classification

ETIM 8.0

EC002301 -
Multifunction
measuring
instrument