



Product designation
Product type designation
Type

Solid state relay
HS1B
single-phase

Input characteristics

Control voltage	3.5...32VDC
Operating voltage limits	

Operating voltage pick-up	V	3.5
Operating voltage drop-out	V	2

Input current at min...max voltage	mA	10...13
Input reverse voltage	V	32

Operating times

Switching-on	Half cycle max
Switching-off	Half cycle max

Output characteristics


Switching mode		Zero crossing
Rated operating voltage	VAC	24...510
Blocking voltage	V	1200
Operational frequency (min...max)	Hz	45...65
Rated operating current AC-51 (resistive load) at 40°C	A	130
Rated operating current AC-51 (resistive load) at 55°C	A	105
Heatsink for use at 40°C and 55°C at rated current AC-51	K/W	≤0.3
Rated operating current AC-53 (motor load) at 40°C	A	32
Operational current min	A	0.05
Non repetitive surge peak on state current t=10ms	A	2100
Off state leakage current	mA	1
On state output voltage drop	V	1.2
Critical rate of rise of off-state voltage dv/dt	V/μs	500
Input - Output isolation	V	4000
Input - Output to metal base	V	4000
Output protection type		VDR
I2t	A2s	22000

Terminal characteristics

Control terminals	Type	Screw M4
Terminals tool	PZ2	
Tightening torque control terminals	Nm	1.2...2
	Ibin	10.6...17.7
Conductor section connectable (control terminals) with 1 or 2 wires min...max		
AWG stranded	n°	18...14
Flexible w/o lug	mm2	0.75...2.5
Flexible c/w insulated spade lug	mm2	0.75...2.5
Load terminals	Type	Screw M5
Load terminals tool	PZ2	
Tightening torque load terminals	Nm	2...3

		Ibin	20.4
Conductor section connectable (load terminals) with 1 or 2 wires min...max			
	AWG stranded	n°	16...10
	Flexible w/o lug	mm2	1.5...6
	Flexible c/w insulated spade lug	mm2	1.5...6
Operating position			
	allowable		Any
Fixing			
			Screw
Ambient conditions			
Temperature			
	Operating temperature		
	min	°C	-55
	max	°C	+90
	Storage temperature		
	min	°C	-55
	max	°C	+125

Dimensions



Certifications and compliance

Certifications

IEC/EN/BS 60947-4-2
IEC/EN/BS 60947-4-3
IEC/EN/BS 62314
IEC/EN/BS 6335-1

Compliance

CSA
cURus
VDE

ETIM classification

EC000066 - Power contactor, AC switching