



Product designation	Micro PLC - Base module		
Product type designation	LRD20RD024		
Auxiliary supply voltage	24VDC		
Number of inputs	Nr.	8 digital + 4 digital/analog	
Number of outputs	Nr.	8 relay	
Max I/O number		20 (12 inputs + 8 outputs) up to 44 with LRE modules	

Power supply

Rated auxil. supply voltage	24VDC		
Operating voltage range	20.4...28.8VDC		
Average current consumption	mA	185	
Power consumption Max	W	5	

Digital inputs

Number of digital input	Nr.	8 + 4 digital/analog	
Rated voltage	V	24VDC	
Input signals		State 0 (OFF)	<5VDC
		State 1 (ON)	>15VDC

Response time		0 to 1 (OFF-ON)	4ms (0.5ms for high speed)
		1 to 0 (ON-OFF)	4ms (0.3ms for high speed)

Analog inputs

Number of analog input	Nr.	4 digital/analog	
Analog input type		Voltage inputs	
Inputs signal range	V	0...10	
Resolution		0.01V	
Bit of conversion	bit	8	

Current consumption at	10VDC	mA	<0.17mA
Input impedance		kΩ	>40
Admissible overload		VDC	28

Sampling time	ms	5...20ms(LADDER), 2...10ms (FBD)	
---------------	----	----------------------------------	--

Maximum cable length	m / ft	≤30m/98ft (shielded wire)	
----------------------	--------	---------------------------	--

Digital outputs

Number of digital output	Nr.	8	
type		Relay	

System resources

Display	LCD display, 4 lines x 16 characters
---------	--------------------------------------

Connections

Terminals type	Screw
----------------	-------

Tightening torque for terminals	max	Nm	0.6
	Max	lbft	0.4

Conductor section	AWG/Kcmil	min	26
		max	14
	IEC	min	mm ² 0.14
		max	mm ² 2.5


Ambient conditions

Temperature	Operating temperature	min	°C	-20
		max	°C	+55
	Storage temperature	min	°C	-40
		max	°C	+70
Relative humidity		%		20...90% without condensation


Housing

Mounting	35mm DIN rail or screw fixing (M4x20mm)
Degree of protection	IP20
Dimensions (W x H x D)	mm 126 x 106 x 59.6
Weight	g 360

Dimensions



Wiring diagrams



① 12VDC for LRD20R D012.

Certifications and compliance

Compliance

CSA C22.2 n° 142
IEC/EN 61131-2
UL508

Certificates

cULus
EAC

ETIM classification

ETIM 8.0	EC001417 - Logic module
----------	----------------------------