



Product designation				Switch disconnecter
Product type designation				GA
Number of poles			Nr.	3
Operating voltage type				AC
Contact characteristics				
IEC Conventional free air thermal current I _{th}			A	32
Rated insulation voltage U _i IEC/EN			V	1000
Rated impulse withstand voltage U _{imp}			kV	8
Operating current I _e				
AC21A				
			400V	A 32
			500V	A 32
			690V	A 32
AC22A				
			400V	A 32
			500V	A 32
			690V	A 32
AC23A				
			400V	A 32
			500V	A 25
			690V	A 25
Power dissipation per pole max			W	0.6
Rated operational power AC23A				
			400V	kW 15
			690V	kW 22
Rated short time current (1s) I _{cw} (rms)			kA	0.8
Conditional short-circuit current (rms)			kA	10
Short-circuit protection with fuse			Class/A	gG32
Making capacity AC23A 400V			A	400
Breaking capacity AC23A 400V			A	320
Mechanical life			cycles	100000
Electrical life AC21A			cycles	100000
Mechanical features				
Operating position			normal allowable	Vertical plan Any
Fixing				Screw / DIN rail 35mm
Terminals				
			type	Pillar
			width	mm 5.6
			height	mm 6.5
			screw	M4
			tool	Phillips 2

Tightening torque for terminals

min	Nm	1.8
max	Nm	2
min	lbin	16
max	lbin	18

Conductor section

IEC min	mm ²	0.75
IEC max	mm ²	16
AWG/kcmil min		18
AWG/kcmil max		6

Ambient conditions

Operating temperature

min	°C	-25
max	°C	55

Storage temperature

min	°C	-40
max	°C	70

Max altitude

m	3000
---	------

Resistance & Protection


Frontal IP degree

IP20


Pollution degree

3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°60947-4-1

IEC/EN 60947-1

IEC/EN 60947-3

UL60947-4-1

Certifications

CCC

CSA C22.2 n°60947-4-1

cULus according to UL60947-4-1

EAC

KEMA

ETIM classification

ETIM 8.0

EC000216 -
Switch
disconnector