




Product designation			Key operated		
Product type designation			KBN		
General characteristics					
General characteristics					
Housing Material			Polymer thermoplastic		
Key shape			Straight		
Contact characteristics					
Type of contact			1NO+1NC		
Thermal current Ith			A	10	
IEC/EN 60947-5-1 designation			A600 Q600		
Rated insulation voltage Ui			V	690	
Rated impulse withstand voltage Uimp			kV	6	
Insulation class			II		
Short-circuit protection with fuse			Class/A	10 gG/SC QUICK FUSE	
Switching speed			min	m/s	0.5
			max	m/s	1.5
IEC Conventional free air thermal current Ith			A	10	
Resistance per pole (average value)			mΩ	<10	
Operations					
Mechanical life			cycles	100000	
B10d			cycles	100000	
Mechanical operation			cycles/h	3600	
Output characteristics					
Mechanical life			cycles	100000	
Mechanical features					
Operating head fixing			Locking bayonet insert		
Operating torque			N	8	
			lb	1.8	
Tightening torque (Max)					
Switch fixing			Nm	2.5	
			lbin	22.1	
Contact terminals			Nm	0.8	
			lbin	7	
Body lid screw fixing			Nm	0.8	
			lbin	7	
Conductor section					
AWG/Kcmil					

LIMIT SWITCH, K SERIES, KEY OPERATED, 1 BOTTOM CABLE ENTRY. DIMENSIONS TO EN 50047, PLASTIC BODY, CONTACTS 1NO+1NC SLOW ACTION. STRAIGHT KEY


			min	16
			max	14
IEC			min	mm ²
			max	mm ²
				1or 2
				2.5
Cable connection				Self-releasing screw terminal
Cable entry				M20 on the bottom
Weight				g
Ambient conditions				92
Pollution degree				3
Temperature				
Operating temperature			min	°C
			max	°C
				-25
				+70
Storage temperature			min	°C
			max	°C
				-40
				+70

Dimensions



Wiring diagrams

Slow action



1NO + 1NC

Certifications and compliance

Compliance

CSA C22.2 n° 14

EN 50047

IEC/EN 60204-1

IEC/EN 60947-1

IEC/EN 60947-5-1

UL508

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000030 - End switch