



Product designation			Hinge operating		
Product type designation			KBP		
General characteristics					
General characteristics					
Housing Material			Polymer thermoplastic		
Rod material			Long solid		
Contact characteristics					
Type of contact			1NO+1NC Slow action		
Thermal current Ith		A	10		
IEC/EN 60947-5-1 designation			A600 Q300		
Rated insulation voltage Ui		V	690		
Rated impulse withstand voltage Uimp		kV	6		
Insulation class			II		
Short-circuit protection with fuse		Class/A	10 gG/SC QUICK FUSE		
Switching speed			min	m/s	0.5
			max	m/s	1.5
IEC Conventional free air thermal current Ith		A	10		
Resistance per pole (average value)		mΩ	<10		
Operations					
Mechanical life		cycles	100000		
B10d		cycles	100000		
Mechanical operation		cycles/h	3600		
Output characteristics					
Mechanical life		cycles	100000		
Mechanical features					
Operating head fixing			Locking bayonet insert		
Operating torque			Ncm	15	
			ozin	21.2	
Tightening torque (Max)					
Switch fixing		Nm	2.5		
		lbin	22.1		
	Contact terminals	Nm	0.8		
		lbin	7		
Body lid screw fixing		Nm	0.8		
		lbin	7		
Conductor section					

LIMIT SWITCH, K SERIES, HINGE OPERATING, 1 BOTTOM CABLE ENTRY. DIMENSIONS TO EN 50047, PLASTIC BODY, CONTACTS 1NO+1NC SLOW ACTION. LONG SOLID SHAFT

AWG/Kcmil

min	16
max	14

IEC

min	mm ²	1 or 2
max	mm ²	2.5

Cable connection

Self-releasing
screw terminal

Cable entry

M20 on the
bottom

Ambient conditions

Pollution degree

3

Temperature


Operating temperature

min	°C	-25
max	°C	+70

Storage temperature


min	°C	-40
max	°C	+70

Dimensions



Wiring diagrams

Slow action



1NO + 1NC

Certifications and compliance

Compliance

CSA C22.2 n° 14

EN 50047

IEC/EN 60204-1

IEC/EN 60947-1

IEC/EN 60947-5-1

UL508

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000030 - End
switch