





Product designation	MODULAR CONTACTOR		
Product type designation	CNM		
Operating voltage type	AC/DC		
Manual control	YES		
Number of poles	4		
Number of DIN modules	2		
Electrical features			
IEC Conventional free air thermal current I _{th}	A	32	
Operational current AC1 and AC-7a ≤400V	A	32	
Operational current AC-3 and AC-7b ≤400V	A	8.5	
Rated insulation voltage U _i IEC/EN	V	440	
Rated impulse withstand voltage U _{imp}	kV	4	
Minimum switching capacity		≥17V ≥50mA	
Power dissipation per pole (average value) I _{th}	W	2.5	
Control circuit			
Auxiliary rated supply voltage U _s		24VAC/DC	
Auxiliary contacts	NO	Nr.	4
Average coil consumption ≤20°C	in-rush	W	3
	holding	W	3
Operating voltage			
pick-up	min	%U _s	85
	max	%U _s	110
drop-out	min	%U _s	20
	max	%U _s	75
Operating times			
Average time			
Closing NO	min	ms	15
	max	ms	45
Opening NO	min	ms	20
	max	ms	70
Operations			
Mechanical life		cycles	3000000
Electrical life AC-3		cycles	500000
Electrical life AC1		cycles	150000
Ambient conditions			
Operating temperature	min	°C	-25
	max	°C	+70

Storage temperature			
	min	°C	-30
	max	°C	80
Max altitude		m	2000
Mechanical features			
Fixing			DIN rail 35mm
Tightening torque for coil terminal			
	max	Nm	0.6
	max	lbin	0.6
Tightening torque for terminals			
	max	Nm	1.2
	max	lbin	0.9
Conductor section			
Coil terminal			
	min	mm ²	1
	max	mm ²	2.5
Power terminal			
	min	mm ²	1
	max	mm ²	10
Terminals tool			PZ2
Weight		g	260
Resistance & Protection			
Frontal IP degree			IP20
Pollution degree			3
Dimensions			



Wiring diagrams



Certifications and compliance

Compliance	IEC/EN 60947-1
	IEC/EN 60947-4-1
	IEC/EN 60947-5-1
	IEC/EN 61095

Certificates	EAC
--------------	-----

ETIM classification

ETIM 8.0	EC000066 - Power contactor, AC switching
----------	--