



Product designation

INDUSTRIAL
RELAYS
HR604C

Product type designation

Contact characteristics

Contact configuration			4 C/O
Rated insulation voltage U_i IEC/EN	V		500
Rated impulse withstand voltage U_{imp}	kV		4
IEC Conventional free air thermal current I_{th}	A		5
Rated current (I_n)	A		5
Relay control voltage	V		24VDC
Max contrallable power in			
	AC-1	W	5
Rated operating power AC-1		VA	1250
Rated operating power AC-15			
	230 VAC	VA	150
Single-phase motor control			
	230VAC	kW	0.37
Rated operating current DC-1			
	30V	A	8
	110V	A	0.3
	220V	A	0.1

Minimum switching load	V / mA		5 / 100
Contact impedance	mΩ		100
Contact material			Ag/Ni

Operating times

Closing	ms		<25
Opening	ms		<25

Operations

Mechanical life	cycles		20000000
Electrical life AC1	cycles		100000

Coil characteristics

Average coil consumption AC at 20°C	VA		1.7
Average coil consumption DC at 20°C	W		1.1

Operating range

Closing	% U_n	75...110
Opening	% U_n	10...30

Maximum cycle frequency	cycles/h		3600
-------------------------	----------	--	------

Mechanical features

Max socket terminal tightening torque	Nm		0.6
Socket screw tightening tool (cross / flat blade)			PH1 / 4.5mm

Conductor section

AWG/Kcmil

min	20
max	14

IEC

min	mm ²	0.5
max	mm ²	2.5

Operating position

normal	Any
--------	-----

Fixing

On 35mm DIN rail and with screw

Ambient conditions

Temperature

Operating temperature

min	°C	-40
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+80

Other features

Indication

Yes

Mechanical contact position indicator


Yes

Mechanical test actuator


Yes

Dimensions


HR60 2C... with socket HR6XS21 - HR6XS22




HR60 4C... with socket HR6XS41 - HR6XS42



HR60 2C... - HR60 4C... with socket HR6XS21S - HR6XS41S



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61810

Certificates

CSA

cURus

EAC

VDE

ETIM classification

ETIM 8.0

EC001437 -
Switching relay