





Product designation			Rope-pull lever with reset button		
Product type designation			RS131310		
General characteristics					
General characteristics					
Housing Material			Polymer thermoplastic		
Contact characteristics					
Type of contact			1NO+1NC		
Thermal current Ith			A	10	
Rated insulation voltage Ui			V	250	
Short-circuit protection with fuse			Class/A	10 gG/SC QUICK FUSE	
IEC Conventional free air thermal current Ith			A	10	
Resistance per pole (average value)			mΩ	<10	
Operations					
Mechanical life			cycles	100000	
Mechanical operation			cycles/h	1800	
Output characteristics					
Mechanical life			cycles	100000	
Mechanical features					
Operating head fixing			Screwed		
Operating torque			N	25	
			Ib	5.6	
Tightening torque (Max)					
Switch fixing			Nm	2.5	
			Ibin	22.1	
Contact terminals			Nm	0.8	
			Ibin	7	
Body lid screw fixing			Nm	0.8	
			Ibin	7	
Conductor section					
AWG/Kcmil			max		14
			IEC		
			min	mm²	1 or 2
			max	mm²	2.5
Cable connection			Self-releasing screw terminal		
Cable entry			PG11		
Weight			g		92
Ambient conditions					

Pollution degree	3		
Temperature			
Operating temperature	min	°C	-25
	max	°C	+70
Storage temperature	min	°C	-40
	max	°C	+70

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN 60204-1

IEC/EN 60947-1

IEC/EN 60947-5-1

ISO 13850; UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000030 - End
switch