



Product designation			Time relay	
Product type designation			L48M	
General characteristics				
Description			Multifunction time relay, multiscale and multivoltage	
Function			Multifunction	
Supply circuit				
Rated auxiliary supply voltage Us			24...240VAC/DC	
Rated auxiliary supply voltage Us AC			min Max	VAC VAC 24 240
DC			min Max	VDC VDC 24 240
Rated frequency			Hz	50/60
Operating voltage range			0.85...1.1 Us	
Maximum power consumption / dissipation			W	6VA
Immunity time for microbreakings			ms	≤40
Timing circuit				
Time setting range			0.05s...10min	
Setting accuracy			%	±5
Repeat accuracy			%	±0.5
Influence of voltage variation			%	±0.5
Resetting time			During timing Elapsed time	ms ms ≥100 ≥65
Relay outputs				
Number of relays			Nr.	2
Contact arrangement			2 delayed C/O	
Maximum switching voltage			VAC	250
IEC Conventional free air thermal current Ith			A	5
UL/CSA and IEC/EN 60947-5-1 designation			B300	
Insulation (input-output)				
Rated insulation voltage Ui			V	250
Power frequency withstand voltage			kV	2
Operations				
Mechanical life			cycles	30000000
Electrical life (with rated load)			cycles	100000
Ambient conditions				
Temperature				
Operating temperature			min max	°C °C -10 +60


Storage temperature

min	°C	-30
max	°C	+80


## Housing

Material	Self-extinguishing polyamide	
Mounting	Plug-in housing with 11-pin socket	
Degree of protection	IP40 on front, IP20 terminals	
Dimensions (W x H x D)	mm	48 x 48 x 90
Weight	g	135

## Dimensions



## Wiring diagrams



$T$  (preset time) =  $T1 + T2$

❶ Contacts "M" and "R" are to be volt free (dry).

## Certifications and compliance

### Compliance

CSA C22.2 n°14  
IEC/EN 61812-1  
UL508

### Certificates

cURus  
EAC

## ETIM classification

ETIM 8.0

EC001439 -  
Timer relay