



Product designation			Switch disconnector	
Product type designation			GA	
Number of poles			Nr.	3
Operating voltage type			AC	
Contact characteristics				
IEC Conventional free air thermal current I <sub>th</sub>			A	160
Rated insulation voltage U <sub>i</sub> IEC/EN			V	1000
Rated impulse withstand voltage U <sub>imp</sub>			kV	8
Operating current I <sub>e</sub>				
AC21A				
			400V	A 160
			500V	A 160
			690V	A 160
AC22A				
			400V	A 160
			500V	A 125
			690V	A 125
AC23A				
			400V	A 125
			500V	A 100
			690V	A 47
Power dissipation per pole max			W	12
Rated operational power AC23A				
			400V	kW 55
			690V	kW 45
Rated short time current (1s) I <sub>cs</sub> (rms)			kA	2.5
Conditional short-circuit current (rms)			kA	50
Short-circuit protection with fuse			Class/A	gG160
Making capacity AC23A 400V			A	1250
Breaking capacity AC23A 400V			A	1000
Mechanical life			cycles	30000
Electrical life AC21A			cycles	1500 (AC23A 400V)
Mechanical features				
Operating position			normal allowable	Vertical plan Any
Fixing			Screw / DIN rail 35mm	
Terminals				
			type	Pillar
			width	mm 12.4
			height	mm 10.4
			screw	M8
			tool	Metric Allen key 4

#### Tightening torque for terminals

min	Nm	5
max	Nm	6
min	lbin	45
max	lbin	54

#### Conductor section

IEC min	mm <sup>2</sup>	4
IEC max	mm <sup>2</sup>	70
AWG/kcmil min		12
AWG/kcmil max		1

#### UL technical data

UL Standard	UL98
-------------	------

#### Minimum enclosure dimensions at rated current

mm	mm	150x140x110
in	in	5.9 x 5.5 x 4.3

#### Ambient conditions

##### Operating temperature

min	°C	-25
max	°C	+55

##### Storage temperature

min	°C	-40
max	°C	+70
	m	3000


##### Max altitude

#### Resistance & Protection


Frontal IP degree	IP20
-------------------	------

Pollution degree	3
------------------	---

#### Dimensions



#### Wiring diagrams



## Certifications and compliance

### Compliance

IEC/EN 60947-1

IEC/EN 60947-3

### Certifications

CCC

EAC

## ETIM classification

ETIM 8.0

EC000216 -  
Switch  
disconnecter