



Product designation  
Product type designation  
Motor type

Soft Starter  
ADXL  
Asynchronous  
three phase

### Electrical features

Supplies voltage	Type of system		Three phase
	Rated supply voltage	V	208...600VAC
	auxiliary supply voltage (Us)		100...240VAC
	Rated frequency	Hz	50/60
Rated starter current Ie		A	115
Rated motor power	IEC ratings (T≤40°C)		
	230VAC	kW	37
	400VAC	kW	55
	500VAC	KW	75
	UL ratings (T≤40°C)		
	220-240VAC	HP	40
	380-415VAC	HP	60
	440-480VAC	HP	75
	550-600VAC	HP	100
Number of controlled phases		Nr.	2
Built-in bypass			Yes
Cooling System			Natural or forced (optional)
Rated insulation voltage Ui		V	600
Programming interface			
Display			Backlit icon LCD display
Programming with NFC technology			Yes
Optical port			Yes
Startup and stop settings			
Startup method			Torque ramp with current limit, Voltage ramp with current limit, Constant torque with current limit
Stop method			Torque ramp, voltage ramp, free-wheel stop
Protections			
Auxiliary supply protection			Voltage too low

Power supply Protection	No power, phase loss, phase sequence, frequency out of limits, minimum and maximum voltage
Motor protection	Overload at starting (trip class 2, 10A, 10, 15, 20, 25, 30, 35 and 40), overload during running (trip class 2, 10A, 10, 15, 20, 25 and 30), locked rotor, current asymmetry, minimum torque (dry run),
Starter protection	Overcurrent, overtemperature, bypass failure, phase shorted, temperature sensor fault, cooling fan fault, maintenance request

Functions	
Built-in bypass	2
Built-in display and keypad	Yes
Languages	Yes
View measurements	6
Torque control	Yes
Adjustable current limit	Yes
Dynamic braking	Yes
Kick Start function	No
Motor overload electronic protection	Yes
Motor protection PTC input	Yes
Protection against phase loss	Yes
Protection against phase inversion	Yes
Protection against locked rotor	Yes
Protection against thyristor overtemperature	Yes
Protection against low load	Yes
Programmable alarm	Yes
Digital inputs	Yes
Analog inputs	Yes
Digital outputs	No
Analog output	Yes
Monitoring communication	No
Optical port for programming	RS485
Event log	Yes
Motor hour counter	Yes
Startup counter	Yes

Clock calendar	Yes
Remote external keypad	No
Plug-in version	Optional

### Input and Output

Digital inputs				
	Number of digital input	Nr.	3	
	Digital input type		2 input with dry contact + 1 input with dry contact or PTC (configurable)	
	Digital input functions		Programmable (motor start, motor stop, freewheel stop, motor preheating, commands lock, alarms inhibition, thermal status reset, keyboard lock, motor selection, user alarm, command)	


Digital outputs				
	Number of digital output	Nr.	3	
	Digital output arrangement		2 x 1 NO (SPST) + 1 C/O (SPDT) Ratings: 2 x 1NO contacts: 3A 250VAC - 3A 30VDC 1 x C/O contact: NO contact 5A 250VAC - 5A 30VDC; NC contact 3A 250VAC - 3A 30VDC Programmable (line contactor, run, global alarm, limits, remote variable, alarm Axx, user alarm Axx, OFF)	
	Digital output functions			

### Ambient conditions

Temperature				
	Operating temperature			
		min	°C	-20
		max	°C	+60°C (with current derating >40°C of 0.5%/°C )
	Storage temperature			
		min	°C	-30
		max	°C	+80

Max altitude	m	1000 without derating (over 1000mt with current derating of 0.5%/100m)
Relative humidity	%	<80%
Pollution degree		2
Installation category		III
<b>Housing</b>		
Mounting		Screw-fixing or 35mm DIN rail with optional accessory EXP8003
IP degree of protection		IP00
Dimensions (W x H x D)	mm	95 x 226 x 182
Weight	Kg	2.9

### Dimensions



### Certifications and compliance

#### Compliance

CSA C22.2 n° 14  
IEC/EN 60947-1  
IEC/EN 60947-4-2  
UL508

---

Certificates

cULus

EAC

RCM

ETIM classification

ETIM 8.0

EC000640 - Soft  
starter