



Product designation				Switching power supplies	
Product type designation				PSE1	
Input characteristics					
Input type				Single-phase	
Rated supply voltage AC			VAC	Multivoltage 100...240	
Operating range					
AC		min	VAC	85	
		Max	VAC	264	
DC		min	VDC	120	
		Max	VDC	375	
Rated frequency			Hz	50/60	
Operational frequency			min	Hz	47
			max	Hz	63
Current consumption Max			mA	1700	
Power dissipation			W	10.5	
Insulation voltage Input/Output			AC	VAC	3000
			DC	VAC	4242
Internal fuse (250VAC)			T3.15A 250VAC		
Output characteristics					
Rated output voltage DC			VDC	24	
Voltage trimming (potentiometer) DC			min	VDC	22.5
			Max	VDC	28.5
Rated output current			A	3	
Rated output power			W	72	
Temperature coefficient			%/°C	±0.03	
Line adjustment			%	±1	
Load adjustment			%	±1	
Efficiency			%	89	
Overload protection			1.4		
Overvoltage protection			min 28.8V / max 32.4V		
Short-circuit protection			Hiccup		
Ripple & noise			mV	100	
Parallel connection			Nr.	No	
Indications					
LED indicator for power on			Yes		
LED indicator for low voltage			No		
Power Rdy (Ready - minimum limit)			No		

Connections

Terminals type	Screw		
Tightening torque for terminals	max	Nm	0.5
	max	lbin	5
Conductor cross section			
AWG/Kcmil	min	AWG	26
	Max	AWG	12
IEC	min	mm ²	0.2
	Max	mm ²	2.5
Cable stripping length		mm	4-5

Ambient conditions

Temperature			
Operating temperature	min	°C	-25
	max	°C	+71
Storage temperature	min	°C	-40
	max	°C	+85
Derating		%/°C	2.5%/°C above 50°C
Relative humidity		%	<95%
Maximum Pollution degree			2
Max altitude		m	5000


Housing

Material	Plastic		
IEC degree of protection	IP20		
Dimensions (W x H x D)	mm	40.5 x 90 x 100	
Weight	g	250	


Installations

Mounting	On 35mm DIN rail		
Installation position	Vertical (other directions with derating)		
Cooling System	Free air convection		

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 107.1.

IEC/EN/BS 61000-6-2

IEC/EN/BS 61000-6-3

IEC/EN/BS 62368-1

UL 508

Certificates

cULus

EAC

RCM

ETIM classification

ETIM 8.0

EC002540 - DC-
power supply