




Product designation			Slotted lever		
Product type designation			KBQ		
General characteristics					
General characteristics					
Housing Material			Polymer thermoplastic		
Contact characteristics					
Type of contact			1NO+1NC Slow action		
Thermal current I _{th}		A	10		
IEC/EN 60947-5-1 designation			A600 Q300		
Rated insulation voltage U _i		V	690		
Rated impulse withstand voltage U _{imp}		kV	6		
Insulation class			II		
Short-circuit protection with fuse		Class/A	10 gG/SC QUICK FUSE		
Switching speed			min	m/s	0.5
			max	m/s	1.5
IEC Conventional free air thermal current I _{th}		A	10		
Resistance per pole (average value)		mΩ	<10		
Operations					
Mechanical life		cycles	100000		
B10d		cycles	100000		
Mechanical operation		cycles/h	3600		
Output characteristics					
Mechanical life		cycles	100000		
Mechanical features					
Operating head fixing			Locking bayonet insert		
Operating torque			Ncm	15	
			ozin	21.2	
Tightening torque (Max)					
Switch fixing		Nm	2.5		
		lbin	22.1		
	Contact terminals	Nm	0.8		
		lbin	7		
Body lid screw fixing		Nm	0.8		
		lbin	7		
Conductor section					
AWG/Kcmil					


	IEC	min	16	
		max	14	
Cable connection		min	mm ²	1or 2
		max	mm ²	2.5
Cable entry		Self-releasing screw terminal		
		M20 on the bottom		
Ambient conditions				
Pollution degree		3		
Temperature				
	Operating temperature	min	°C	-25
		max	°C	+70
	Storage temperature	min	°C	-40
		max	°C	+70

Dimensions



Wiring diagrams

Slow action



1NO + 1NC

Certifications and compliance

Compliance

CSA C22.2 n° 14

EN 50047

IEC/EN 60204-1

IEC/EN 60947-1

IEC/EN 60947-5-1

UL508

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000030 - End switch