

Product type designation			GX20
General characteristics			
Switching diagram			25
N° of elements			2
Contact characteristics			
Rated insulation voltage Ui			
	IEC/EN	V	690
	UL/CSA	V	600
Rated impulse withstand voltage Uimp			kV 6
Conventional free air thermal current Ith			
	UL/CSA	A	15
Rated operational voltage			V 440
Maximum fuse size for short-circuit protection In (gG)			
	25kA	A	16
Rated short time current Icw			
	1s	A	250
Operational current Ie IEC/EN			
AC1/AC21A			A 20
AC15			
	110V	A	10
	220/230V	A	8
	660/690V	A	3.7
Rated operational power in AC			
Single-phase AC-3			
	380/440V	kW	3
Three-phase AC23A			
	380/440V	kW	7.5
Single-phase AC23A			
	380/440V	kW	3.5
Rated operational current in DC			
DC21A			
	48V	A	20
	60V	A	20
	110V	A	4
	440V	A	0.25
DC23A (poles in series)			
	24V	A	20 (1)
	48V	A	20 (2)
	60V	A	20 (3)
	110V	A	10 (3)
	220V	A	8 (4)
DC13			
	24V	A	20
	48V	A	16
	60V	A	12
	110V	A	1
	220V	A	0.4
	440V	A	0.15
Mechanical features			
Terminals screw			M3
Tightening torque for terminals max			Nm 0.8
Conductor size			

AWG - Rigid cable

min	AWG	20
Max	AWG	14

AWG - Flexible cable

min	AWG	20
-----	-----	----

Conductor size (IEC) - Flexible cable

min	mm <sup>2</sup>	0.5
Max	mm <sup>2</sup>	2.5

Conductor size (IEC) - Rigid cable

Max	mm <sup>2</sup>	2.5
-----	-----------------	-----

Mechanical life

cycles	5x10 <sup>6</sup>
--------	-------------------

#### UL technical data

Motor power for direct-on-line control

for three-phase motor

240V	HP	3
480V	HP	5
600V	HP	5

for single-phase motor

120V	HP	0.75
240V	HP	1.5

#### Ambient conditions

Temperature

Operating temperature

min	°C	-25
max	°C	+55

Storage temperature

min	°C	-40
max	°C	+70

#### Resistance & Protection

Frontal IP degree

IP65

Terminals IP degree

IP20

#### ETIM classification

ETIM 8.0

EC001029 -  
Selector switch,  
complete