





Product designation			Time relay	
Product type designation			L48TPB	
General characteristics				
Description			On delay time relay, multiscale and multivoltage, plug-in version	
Function			On delay	
Supply circuit				
Rated auxiliary supply voltage U_s			24VAC/DC	
Rated frequency		Hz	50/60	
Operating voltage range			0.85...1.1 U_s	
Maximum power consumption / dissipation		W	6VA	
Immunity time for microbreakings		ms	≤40	
Timing circuit				
Time setting range			0.05s...10min	
Setting accuracy		%	±5	
Repeat accuracy		%	±0.5	
Influence of voltage variation		%	±0.5	
Resetting time			During timing	ms ≥100
			Elapsed time	ms ≥65
Relay outputs				
Number of relays			Nr.	2
Contact arrangement			2 delayed C/O or 1 instantaneous C/O + 1 delayed C/O	
Maximum switching voltage			VAC	250
IEC Conventional free air thermal current I_{th}			A	5
UL/CSA and IEC/EN 60947-5-1 designation			B300	
Insulation (input-output)				
Rated insulation voltage U_i			V	250
Power frequency withstand voltage			kV	2
Operations				
Mechanical life			cycles	30000000
Electrical life (with rated load)			cycles	100000
Ambient conditions				
Temperature				
Operating temperature		min	°C	-10
		max	°C	+60
Storage temperature		min	°C	-30
		max	°C	+80
Housing				

Material	Self-extinguishing polyamide	
Mounting	Plug-in housing with 8-pin socket	
Degree of protection	IP40 on front, IP20 terminals	
Dimensions (W x H x D)	mm	48 x 48 x 90
Weight	g	124

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°14
IEC/EN 61812-1
UL508

Certificates

cURus
EAC

ETIM classification

ETIM 8.0

EC001439 -
Timer relay