



Start-up priority change relay.  
Possible starting of stand-by motor. Modular version  
LVMP10  
Start-up priority change relay.  
Possible starting of stand-by motor

Product designation

Product type designation

Function

#### Auxiliary supply

|                                      |                  |     |       |
|--------------------------------------|------------------|-----|-------|
| Supply voltage Type                  | Single voltage   |     |       |
| Rated auxiliary supply voltage $U_s$ |                  |     |       |
| AC                                   | min              | VAC | 220   |
|                                      | Max              | VAC | 240   |
| Operating voltage range              | 0.85...1.1 $U_s$ |     |       |
| Rated frequency                      |                  | Hz  | 50/60 |
| Power consumption Max                |                  | VA  | 4.8   |
| Power dissipation Max                |                  | W   | 3     |

#### Relay outputs

|                                                    |                                              |                  |
|----------------------------------------------------|----------------------------------------------|------------------|
| Number of relays                                   | Nr.                                          | 2                |
| Relay state                                        | Normally de-energised, energises at tripping |                  |
| Contact arrangement                                | 2 x 1NO-SPST contact                         |                  |
| Rated operational voltage AC (IEC)                 | VAC                                          | 250              |
| Maximum switching voltage                          | VAC                                          | 400              |
| IEC Conventional free air thermal current $I_{th}$ | A                                            | 8                |
| UL/CSA and IEC/EN 60947-5-1 designation            | B300                                         |                  |
| Electrical life (with rated load)                  | cycles                                       | $10^5$           |
| Mechanical life                                    | cycles                                       | $30 \times 10^6$ |

#### Indications

|            |                                                    |
|------------|----------------------------------------------------|
| Indication | 1 green LED for power on 1 red LED for relay state |
|------------|----------------------------------------------------|

#### Functions

|                                                         |    |
|---------------------------------------------------------|----|
| 3 detecting electrodes (MIN, MAX and COM)               | No |
| 5 detecting electrodes (MIN1, MAX1, MIN2, MAX2 and COM) | No |
| Sensitivity adjustment 2.5...50k $\Omega$               | No |
| Sensitivity adjustment 2.5...100k $\Omega$              | No |
| Sensitivity adjustment 2.5...200k $\Omega$              | No |

|                                                                  |    |
|------------------------------------------------------------------|----|
| Adjustable sensitivity full-scale value 25-50-100-200 k $\Omega$ | No |
| Separate sensitivity adjustment for MAX probe (foam detection)   | No |
| Emptying function                                                | No |
| Filling function                                                 | No |
| Emptying function with MIN and/or MAX alarm                      | No |
| Filling function with MIN and/or MAX alarm                       | No |
| Emptying function with pump priority change                      | No |
| Filling function with pump priority change                       | No |
| Tank filling, well drawing and alarm                             | No |
| Filling-emptying adjustment selector                             | No |
| Programming selector for 5 different                             | No |
| Motor start-up priority change                                   | No |

#### Connections

| Terminals type                  |     |      | Screw |
|---------------------------------|-----|------|-------|
| Tightening torque for terminals |     |      |       |
|                                 | max | Nm   | 0.8   |
|                                 | max | lbin | 7     |

|                         |            |                                    |          |
|-------------------------|------------|------------------------------------|----------|
| Conductor cross section |            |                                    |          |
| AWG/Kcmil               | min<br>Max | AWG<br>AWG                         | 24<br>12 |
| IEC                     | min<br>Max | mm <sup>2</sup><br>mm <sup>2</sup> | 0.2<br>4 |

#### Insulations

|                                           |    |     |
|-------------------------------------------|----|-----|
| Rated insulation voltage $U_i$            | V  | 415 |
| Rated impulse withstand voltage $U_{imp}$ | kV | 4   |
| Operating frequency withstand voltage     | kV | 2.5 |


#### Ambient conditions

|                       |            |          |            |
|-----------------------|------------|----------|------------|
| Temperature           |            |          |            |
| Operating temperature | min<br>max | °C<br>°C | -20<br>+60 |
| Storage temperature   | min<br>max | °C<br>°C | -30<br>+80 |

#### Housing


|                          |    |                                                                   |
|--------------------------|----|-------------------------------------------------------------------|
| Execution                |    | Modular DIN rail mounting                                         |
| N° of modules            |    | 3                                                                 |
| Material                 |    | Self-extinguishing polyamide                                      |
| Mounting                 |    | 35mm DIN rail (IEC/EN 60715) or by screws using extractable clips |
| IEC degree of protection |    | IP40 on front / IP20 on terminals                                 |
| Dimensions (W x H x D)   | mm | 53.5 x 104.7 x 64.9                                               |
| Weight                   | g  | 250                                                               |

#### Dimensions




## Wiring diagrams

## 2-wire connection



C1 = Primary  
C2 = Secondary / Standby

### 3-wire connection



C1 = Start Primary  
C2 = Start Standby  
C3 = Stop Primary  
C4 = Stop Standby

## Certifications and compliance

## Compliance

CSA C22.2 n° 14

IEC/EN 60255-5

IEC/EN 61000-6-2

IEC/EN 61000-6-3

UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC001447 - (Fill)  
level monitoring  
relay