



Product designation

Direct-on-line
starter

Product type designation

M0P00912...10

Electrical features

Relay adj range	A	6-10
IEC technical characteristics ($\leq 440V$)		
	I _e kW	A kW
	10	3...4

Components

Starter enclosure standard supplied	M0PA
Contactor standard supplied	BG0910A
Thermal relay standard supplied	RF910

UL technical data

Maximum UL/CSA horsepower ratings single-phase	110V-120V	HP	0.5
	220V-240V	HP	1.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole	200V-208V	HP	2
	220V-240V	HP	3
	440V-480V	HP	5
	550V-600V	HP	5

Mechanical features

Weight	g	760
--------	---	-----

Ambient conditions


Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70

Resistance & Protection


Frontal IP degree	IP65
-------------------	------

Dimensions

DIRECT-ON-LINE-STARTER, 6...10A (3...4KW AT 400V), IP65, CONTACTOR COIL VOLTAGE 400VAC 50/60HZ, NON-METALLIC ENCLOSURE, WITH THERMAL OVERLOAD RELAY, WITH START AND STOP/RESET BUTTONS



Wiring diagrams



I = Start; O = Stop/Reset

Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

UL508 CSA C22.2 n° 14

Certificates

CSAus

cULys

EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination