



Product designation

Power contactor

Product type designation

BFK115

Contact characteristics

Number of poles	Nr.	3
Rated insulation voltage U_i IEC/EN	V	690
Rated impulse withstand voltage U_{imp}	kV	8
Operational frequency	min Hz	25
	max Hz	400
IEC Conventional free air thermal current I_{th}	A	160
Rated operational power AC-6b ($T \leq 40^\circ C$)	230V kvar	45
	400V kvar	75
	440...480V kvar	85
	690V kvar	135
Short-time allowable current for 10s (IEC/EN60947-1)	A	920
Protection fuse	gG (IEC)	A 160
Making capacity (RMS value)	A	1500
Breaking capacity at voltage	440V A	1200
	500V A	850
	690V A	905
Resistance per pole (average value)	mΩ	0.45
Power dissipation per pole (average value)	I_{th} W	11.5
Tightening torque for terminals	min Nm	6
	max Nm	7
	min lbin	4.4
	max lbin	5.2
Tightening torque for coil terminal	min Nm	0.8
	max Nm	1
	min lbin	0.59
	max lbin	0.74
Max number of wires simultaneously connectable	Nr.	2
Conductor section	AWG/Kcmil	
	max	2/0
Flexible w/o lug conductor section	min mm ²	1.5
	max mm ²	70
Flexible c/w lug conductor section	min mm ²	1.5

Power terminal protection according to IEC/EN 60529		max	mm ²	70
				IP20 front
Mechanical features				
Operating position		normal allowable		Vertical plan ±30°
Fixing				Screw / DIN rail 35mm
Weight			g	2095
Conductor section				
AWG/kcmil conductor section		max		2/0
Operations				
Mechanical life			cycles	15000000
Electrical life			cycles	1200000
Safety related data				
Performance level B10d according to EN/ISO 13489-1				
		rated load	cycles	400000
		mechanical load	cycles	15000000
EMC compatibility				yes
AC coil operating				
Rated AC voltage at 50/60Hz			V	230
AC operating voltage				
of 50/60Hz coil powered at 50Hz				
pick-up		min	%Us	80
		max	%Us	110
drop-out				
		min	%Us	20
		max	%Us	55
of 50/60Hz coil powered at 60Hz				
pick-up		min	%Us	85
		max	%Us	110
drop-out				
		min	%Us	40
		max	%Us	55
AC average coil consumption at 20°C				
of 50/60Hz coil powered at 50Hz		holding	VA	20
of 50/60Hz coil powered at 60Hz		in-rush	VA	300
		holding	VA	17
of 60Hz coil powered at 60Hz		in-rush	VA	300
		holding	VA	20
Dissipation at holding ≤20°C 50Hz			W	6.5
Max cycles frequency				
Mechanical operation			cycles/h	1500
Operating times				
Average time for Us control in AC				
Closing NO		min	ms	16

CONTACTOR PARA CORRECCIÓN DEL FACTOR DE POTENCIA CON CIRCUITO DE CONTROL EN AC, TIPO BFK (CON RESISTENCIAS LIMITADORAS), POTENCIA NOMINAL MÁXIMA (IEC) 400V = 75KVAR, BOBINA 230VAC 50/60HZ

Opening NO	max	ms	32
	min	ms	9
	max	ms	24

UL technical data

General USE

Contactor

AC current	A	160
------------	---	-----

Ambient conditions

Temperature

Operating temperature

min	°C	-50
max	°C	70

Storage temperature

min	°C	-60
max	°C	80

Max altitude


m	3000
---	------

Resistance & Protection

Pollution degree


3

Dimensions



Wiring diagrams

CONTACTOR PARA CORRECCIÓN DEL FACTOR DE POTENCIA CON CIRCUITO DE CONTROL EN AC, TIPO BFK (CON RESISTENCIAS LIMITADORAS), POTENCIA NOMINAL MÁXIMA (IEC) 400V = 75KVAR, BOBINA 230VAC 50/60HZ



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN/BS 60947-1

IEC/EN/BS 60947-4-1

UL 60947-1

UL 60947-4-1

Certificates

CCC

cULus

ETIM classification

ETIM 8.0

EC001079 -
Capacitor
contactor