



Product designation

Power contactor

Product type designation

BFK65

Contact characteristics

Number of poles		Nr.	3
Rated insulation voltage Ui IEC/EN		V	690
Rated impulse withstand voltage Uimp		kV	8
Operational frequency		min	Hz 25
		max	Hz 400
IEC Conventional free air thermal current Ith		A	100
Rated operational power AC-6b (T≤40°C)		230V	kvar 26
		400V	kvar 45
		440...480V	kvar 50
		690V	kvar 56
Short-time allowable current for 10s (IEC/EN60947-1)		A	640
Protection fuse		gG (IEC)	A 100
Making capacity (RMS value)		A	650
Breaking capacity at voltage		440V	A 520
		500V	A 425
		690V	A 376
Resistance per pole (average value)		mΩ	0.8
Power dissipation per pole (average value)		Ith	W 8
Tightening torque for terminals		min	Nm 4
		max	Nm 5
		min	Ibin 2.95
		max	Ibin 3.69
Tightening torque for coil terminal		min	Nm 0.8
		max	Nm 1
		min	Ibin 0.8
		max	Ibin 0.74
Max number of wires simultaneously connectable		Nr.	2
Conductor section		AWG/Kcmil	
		max	2
Flexible w/o lug conductor section		min	mm² 1.5
		max	mm² 35
Flexible c/w lug conductor section		min	mm² 1.5

	max	mm ²	35
Power terminal protection according to IEC/EN 60529			IP20 front
Mechanical features			
Operating position	normal allowable		Vertical plan ±30°
Fixing			Screw / DIN rail 35mm
Weight		g	1090
Conductor section			
AWG/kcmil conductor section	max		2
Operations			
Mechanical life		cycles	15000000
Electrical life		cycles	400000
Safety related data			
Performance level B10d according to EN/ISO 13489-1			
	rated load	cycles	400000
	mechanical load	cycles	15000000
EMC compatibility			yes
AC coil operating			
Rated AC voltage at 50/60Hz		V	400
AC operating voltage			
of 50/60Hz coil powered at 50Hz			
pick-up	min	%Us	80
	max	%Us	110
drop-out	min	%Us	20
	max	%Us	55
of 50/60Hz coil powered at 60Hz			
pick-up	min	%Us	85
	max	%Us	110
drop-out	min	%Us	20
	max	%Us	55
AC average coil consumption at 20°C			
of 50/60Hz coil powered at 50Hz			
	in-rush	VA	210
	holding	VA	15
of 50/60Hz coil powered at 60Hz			
	in-rush	VA	195
	holding	VA	13
of 60Hz coil powered at 60Hz			
	in-rush	VA	210
	holding	VA	15
Dissipation at holding ≤20°C 50Hz		W	5
Max cycles frequency			
Mechanical operation		cycles/h	3600
Operating times			
Average time for Us control			
in AC			
Closing NO			

CONTACTOR PARA CORRECCIÓN DEL FACTOR DE POTENCIA CON CIRCUITO DE CONTROL EN AC, TIPO BFK (CON RESISTENCIAS LIMITADORAS), POTENCIA NOMINAL MÁXIMA (IEC) 400V = 45KVAR, BOBINA 400VAC 50/60HZ

	Opening NO	min	ms	12
		max	ms	28
		min	ms	8
		max	ms	22
in DC				
	Closing NO	min	ms	40
		max	ms	85
	Opening NO	min	ms	20
		max	ms	55

UL technical data

General USE

Contactor

AC current A 100

Ambient conditions

Temperature

Operating temperature

min °C -50
max °C 70

Storage temperature

min °C -60
max °C 80

Max altitude


m 3000

Resistance & Protection


Pollution degree

3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1
CSA C22.2 n° 60947-4-1
IEC/EN/BS 60947-1
IEC/EN/BS 60947-4-1
UL 60947-1
UL 60947-4-1

Certificates

CCC
cULus

ETIM classification

ETIM 8.0

EC001079 -
Capacitor
contactor