



Product designation

Power contactor

Product type designation

BFK95

Contact characteristics

Number of poles	Nr.	3
Rated insulation voltage U_i IEC/EN	V	690
Rated impulse withstand voltage U_{imp}	kV	8
Operational frequency	min Hz	25
	max Hz	400
IEC Conventional free air thermal current I_{th}	A	140
Rated operational power AC-6b ($T \leq 40^\circ C$)	230V kvar	34
	400V kvar	60
	440...480V kvar	75
	690V kvar	80
Short-time allowable current for 10s (IEC/EN60947-1)	A	760
Protection fuse	gG (IEC)	A
		125
Making capacity (RMS value)	A	1200
Breaking capacity at voltage	440V A	1100
	500V A	775
	690V A	745
Resistance per pole (average value)	mΩ	0.45
Power dissipation per pole (average value)	I_{th} W	8.8
Tightening torque for terminals	min Nm	6
	max Nm	7
	min lbin	4.4
	max lbin	5.2
Tightening torque for coil terminal	min Nm	0.8
	max Nm	1
	min lbin	0.59
	max lbin	0.74
Max number of wires simultaneously connectable	Nr.	2
Conductor section	AWG/Kcmil	
	max	2/0
Flexible w/o lug conductor section	min mm ²	1.5
	max mm ²	70
Flexible c/w lug conductor section	min mm ²	1.5

	max	mm ²	70
Power terminal protection according to IEC/EN 60529			IP20 front
Mechanical features			
Operating position	normal allowable		Vertical plan ±30°
Fixing			Screw / DIN rail 35mm
Weight		g	2095
Conductor section			
AWG/kcmil conductor section	max		2/0
Operations			
Mechanical life		cycles	15000000
Electrical life		cycles	400000
Safety related data			
Performance level B10d according to EN/ISO 13489-1			
	rated load	cycles	400000
	mechanical load	cycles	15000000
EMC compatibility			yes
AC coil operating			
Rated AC voltage at 50/60Hz		V	230
AC operating voltage			
of 50/60Hz coil powered at 50Hz			
pick-up	min	%Us	80
	max	%Us	110
drop-out	min	%Us	20
	max	%Us	55
of 50/60Hz coil powered at 60Hz			
pick-up	min	%Us	85
	max	%Us	110
drop-out	min	%Us	40
	max	%Us	55
AC average coil consumption at 20°C			
of 50/60Hz coil powered at 50Hz	holding	VA	20
of 50/60Hz coil powered at 60Hz	in-rush	VA	300
	holding	VA	17
of 60Hz coil powered at 60Hz	in-rush	VA	300
	holding	VA	20
Dissipation at holding ≤20°C 50Hz		W	6.5
Max cycles frequency			
Mechanical operation		cycles/h	1500
Operating times			
Average time for Us control			
in AC			
Closing NO	min	ms	16

CONTACTOR PARA CORRECCIÓN DEL FACTOR DE POTENCIA CON CIRCUITO DE CONTROL EN AC, TIPO BFK (CON RESISTENCIAS LIMITADORAS), POTENCIA NOMINAL MÁXIMA (IEC) 400V = 60KVAR, BOBINA 230VAC 50/60HZ

Opening NO	max	ms	32
	min	ms	9
	max	ms	24

UL technical data

General USE

Contactor	AC current	A	140
-----------	------------	---	-----

Ambient conditions

Temperature

Operating temperature	min	°C	-50
	max	°C	70


Storage temperature	min	°C	-60
	max	°C	80

Max altitude	m	3000
--------------	---	------


Resistance & Protection

Pollution degree	3
------------------	---

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN/BS 60947-1

IEC/EN/BS 60947-4-1

UL 60947-1

UL 60947-4-1

Certificates

CCC

cULus

ETIM classification

ETIM 8.0

EC001079 -
Capacitor
contactor