





Product designation		SRA
Product type designation		Single function
General characteristics		
General characteristics		
Functions		Devices two hands
Contact characteristics		
Type of contact		2NO+1PNP
Operations		
Mechanical life	cycles	>10 ⁷
Auxiliary supply		
Nominal auxiliary voltage supply		24VDC
Operating range	V	22...26VDC / 20.4...27.6VAC
Overvoltage category		III
Insulation voltage		kV 4
Protections		Signaling output protected from overload
Input characteristics		
Number of inputs	Nr.	2
Input current	mA	Typical 4.3
Input voltage		0-30VDC
Output characteristics		
Number of safe outputs NO	Nr.	2
Number of safe outputs NC	Nr.	0
Number of feedback outputs		Nr. 1PNP
Output type		Relays with forcibly guided contacts
Output contacts ratings		AC1 250V: 6A-2000VA AC15 230V: 5A DC13 24V: 2A
UL 508 ratings		Pilot duty: B300-Q300
Mechanical life	cycles	>10 ⁷
Electrical life AC1 at 360 commutations/h	cycles	10 ⁵
Safety parameters		
ISO 13849-1 security category		Cat. 4
ISO 13849-1 performance level		PLe
Mechanical features		
Fixing		35mm DIN rail
Weight	g	150
Ambient conditions		

Protection degree				IP40 on front IP20 on terminals
Pollution degree				2
Temperature				
Operating temperature		min	°C	-25
		max	°C	+55
		Storage temperature		
		min	°C	-30
		max	°C	+70
Relative humidity			%	≤95

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

EN/BS 62061

EN/ISO/BS 13849-1

Certificates

cULus

TUV

ETIM classification

ETIM 8.0

EC001449 -
Device for
monitoring of
safety-related
circuits