





Product designation			Monoblock potentiometers	
Product type designation			LPCPA	
General characteristics				
Type of positions			Potentiometer	
Resistance value		KΩ	10	
Material			Polyamide - Resistive material: cermet	
IEC degree of protection			IP66, IP67; IP96K on front and IP20 on rear	
Electrical characteristics				
Rated insulation voltage Ui IEC/EN		V	250VAC	
Rated impulse withstand voltage Uimp		kV	4	
Max power		W	1	
Mechanical features				
Mechanical travel		°	290	
Weight		g	40	
UL technical data				
UL degree of protection			1, 2, 3R, 4, 4X, 12, 12K on front	
Ambient conditions				
Temperature		Operating temperature		
		min	°C	-25
		max	°C	+70
		Storage temperature		
		min	°C	-40
		max	°C	+85
Resistance & Protection				
Resistance tolerance		%	±10%	
Dimensions				



## Wiring diagrams



Certifications and compliance

Compliance	CSA C22.2 n° 14
	IEC/EN/BS 60947-1
	IEC/EN/BS 60947-5-1
	UL508

Certificates	CCC
	cULus
	EAC

ETIM classification

ETIM 8.0	EC001027 - Potentiometer for command devices
----------	---