




Product designation			Time relay	
Product type designation			L48TPB	
General characteristics				
Description			On delay time relay, multiscale and multivoltage, plug-in version	
Function			On delay	
Supply circuit				
Rated auxiliary supply voltage $U_s$			220...240VAC	
Rated auxiliary supply voltage $U_s$ AC			min	VAC 220
			Max	VAC 240
Rated frequency			Hz	50/60
Operating voltage range			0.85...1.1 $U_s$	
Maximum power consumption / dissipation			W	6VA
Immunity time for microbreakings			ms	≤40
Timing circuit				
Time setting range			0.05s...10min	
Setting accuracy			%	±5
Repeat accuracy			%	±0.5
Influence of voltage variation			%	±0.5
Resetting time			During timing	ms ≥100
			Elapsed time	ms ≥65
Relay outputs				
Number of relays			Nr.	2
Contact arrangement			2 delayed C/O or 1 instantaneous C/O + 1 delayed C/O	
Maximum switching voltage			VAC	250
IEC Conventional free air thermal current $I_{th}$			A	5
UL/CSA and IEC/EN 60947-5-1 designation			B300	
Insulation (input-output)				
Rated insulation voltage $U_i$			V	250
Power frequency withstand voltage			kV	2
Operations				
Mechanical life			cycles	30000000
Electrical life (with rated load)			cycles	100000
Ambient conditions				
Temperature			Operating temperature	
			min	°C -10
			max	°C +60

Storage temperature


min	°C	-30
max	°C	+80

Housing		
Material	Self-extinguishing polyamide	
Mounting	Plug-in housing with 8-pin socket	
Degree of protection	IP40 on front, IP20 terminals	
Dimensions (W x H x D)	mm	48 x 48 x 90
Weight	g	124

Dimensions



Wiring diagrams



Certifications and compliance

Compliance	CSA C22.2 n°14
	IEC/EN 61812-1
	UL508
Certificates	cURus
	EAC

ETIM classification

ETIM 8.0	EC001439 - Timer relay
----------	------------------------