



Level control  
relay for  
emptying  
function. Dual  
voltage. Plug-in  
version  
LV2E  
Emptying

Product designation

Product type designation

Function

#### Auxiliary supply

Supply voltage Type		Dual voltage
Rated voltage Us		220... 240VAC/380... 415VAC
Operating voltage range		0.85...1.1 Us
Rated frequency	Hz	50/60
Power consumption Max	VA	5.5
Power dissipation Max	W	2.8

#### Output characteristics

Number of connectable electrodes	Nr.	3
Type of electrode		Electrode and electrode holders: SN1 / SCM / CGL / PS31 / PS3S or similar
Electrode voltage		9VAC (voltage between probes)
Sensitivity	kΩ	7...8 fixed

#### Time delay


Tripping time	s	≤0.05
Resetting time	s	≤0.1

#### Relay outputs


Number of relays	Nr.	1
Relay state		Normally de- energised, energises at tripping
Contact arrangement		1 changeover contact C/O- SPDT
Rated operational voltage AC (IEC)	VAC	220
Maximum switching voltage	VAC	380
IEC Conventional free air thermal current Ith	A	5
UL/CSA and IEC/EN 60947-5-1 designation		B300
Electrical life (with rated load)	cycles	2.5 x 10 <sup>5</sup>
Mechanical life	cycles	50x10 <sup>6</sup>

#### Indications

Indication			1 red LED for relay state		
Connections					
Terminals type			plug-in		
Insulations					
Rated insulation voltage Ui			V	415	
Rated impulse withstand voltage Uimp			kV	5	
Operating frequency withstand voltage			kV	2	
Ambient conditions					
Temperature					
Operating temperature			min	°C	-20
			max	°C	+60
Storage temperature			min	°C	-30
			max	°C	+80
Housing					
Execution			11-pin plug-in housing (socket S11)		
Material			Self-extinguishing polycarbonate		
Mounting			35mm DIN rail (IEC/EN 60715) or 11-pin plug-in housing		
IEC degree of protection			IP30		
Dimensions (W x H x D)			mm	38 x 76 x 70	
Weight			g	266	
Dimensions					



## Wiring diagrams



## Certifications and compliance

### Compliance

IEC/EN 60255-5

### Certificates

EAC

## ETIM classification

### ETIM 8.0

EC001447 - (Fill)  
level monitoring  
relay