




Product designation			Fuse holder	
Product type designation			FB	
Number of DIN modules			1	
Operating voltage type			DC	
Electrical features				
IEC maximum rated current (In)		A	32	
IEC maximum rated voltage (Un)		V	1500	
Suitable for IEC fuse class		gPV		
IEC Utilization category		DC20B 1500VDC		
Power dissipation Max		W	8	
Derating factor of rated current In for different ambient temperature		20°C	1	
		30°C	0.98	
		40°C	0.94	
		50°C	0.88	
		60°C	0.83	
		70°C	0.75	
Voltage range for status indicator		800...1500VDC		
Rated current (In)		A	32	
Ambient conditions				
Operating temperature		min	°C	-20
		max	°C	+70
Storage temperature		min	°C	-40
		max	°C	+80
Max altitude		m	3000	
Mechanical features				
Operating position		normal	Vertical plan	
		allowable	Any	
Fixing		35mm DIN rail		
Tightening torque for terminals		max	Nm	2.5
		max	Ibin	22
Conductor section		Flexible max (IEC)	mm²	1x10
		- Flexible max (AWG/kcmil)		1x8
		Rigid max (IEC)	mm²	1x16
		- Rigid max (AWG/kcmil)		1x6
Weight		g	110	
Resistance & Protection				
Frontal IP degree		IP20		
Dimensions				



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN/BS 60947-3

ETIM classification

ETIM 8.0

EC002705 -
Holder for
cylindrical fuse