



Product designation			Three-phase energy meters
Product type designation			DMED305T2
Type			Three-phase with and without neutral
DIN rail module number			4
Auxiliary supply U_s			
Operational frequency			
	min	Hz	50
	max	Hz	60
Power consumption			
	Max	VA	3.5
Power dissipation Max			
		W	2.7
Measuring voltage inputs			
Rated voltage (U_e)			
	phase-phase	VAC	380...415
	phase-neutral	VAC	220...240
Operating voltage range			
	phase-phase	VAC	323...456
	phase-neutral	VAC	187...264
Connection method			Via CT
Current			
IEC maximum (I_{max})			A 5
IEC minimum (I_{min})			A 0.05
IEC rated (I_{ref-Ib})			A 5
IEC start (I_{st})			mA 0.005
Transition (I_{tr})			A 0.25
Accuracy			
	Active energy		Class 0.5s (IEC/EN 62053-22)
	Reactive energy		Class 2 (IEC/EN 62053-23)
Output characteristics			
LED Pulse rate			pulse/kWh 1000
LED Pulse duration			ms 30
Static output pulse rate			pulse/kWh 0.1-1-10-100 programmable
Static output pulse duration			ms 100
Static output external voltage			VDC 10...30
Static outputs Maximum current			mA 50
Insulations			
Rated insulation voltage U_i IEC/EN			V 250
Rated impulse withstand voltage U_{imp}			kV 6
Operating frequency withstand voltage			kV 4


Mechanical features

Housing type	Polyamide		
Terminals type	Fixed		
Conductor cross section	min	mm ²	0.2
			4 for supply voltage measurement;
	Max	mm ²	2.5 for current measurement
	min	AWG	24
	Max	AWG	12
Tightening torque (Max)		Nm	0.8
		lbin	7
Fixing	Din rail		
Weight		g	332

Ambient conditions


Temperature	Operating temperature	min	°C	-25
		max	°C	+55
	Storage temperature	min	°C	-25
		max	°C	+70
Relative humidity			%	<80
Maximum Pollution degree				2

Dimensions




Wiring diagrams


Single-phase





Two-phase



Three-phase with or without neutral




Three-phase without neutral in ARON connection



Tariff input



Pulse output 30VDC 50mA for DME D305 T2



RS485 for DME D330



M-Bus for DME D332



Certifications and compliance

Compliance

IEC/EN 50470-1

IEC/EN 61010-1

IEC/EN 61010-2-030

Certificates

EAC

RCM

ETIM classification

ETIM 8.0

EC001506 -
Kilowatt-hour
meter