





Product designation			Monoblock potentiometers
Product type designation			LPCPA
General characteristics			
Type of positions			Potentiometer
Resistance value		KΩ	1
Material			Polyamide - Resistive material: cermet
IEC degree of protection			IP66, IP67; IP96K on front and IP20 on rear
Electrical characteristics			
Rated insulation voltage Ui IEC/EN		V	250VAC
Rated impulse withstand voltage Uimp		kV	4
Max power		W	1
Mechanical features			
Mechanical travel		°	290
Weight		g	40
UL technical data			
UL degree of protection			1, 2, 3R, 4, 4X, 12, 12K on front
Ambient conditions			
Temperature			
Operating temperature			
		min	°C -25
		max	°C +70
Storage temperature			
		min	°C -40
		max	°C +85
Resistance & Protection			
Resistance tolerance		%	±10%
Dimensions			



Wiring diagrams



Certifications and compliance	
Compliance	CSA C22.2 n° 14
	IEC/EN/BS 60947-1
	IEC/EN/BS 60947-5-1
	UL508
Certificates	CCC
	cULus
	EAC
ETIM classification	
ETIM 8.0	EC001027 - Potentiometer for command devices