



## Product designation

LED elements  
steady light  
LPXLP

Product type designation

## General characteristics

Colour Green

## Electrical characteristics

Supply voltage (AC)	V	12...30
---------------------	---	---------

Supply voltage (DC)	V	12...30
---------------------	---	---------

## Operations

Electrical life	hours	100000
-----------------	-------	--------

## Mechanical features

Tightening torque for terminals max	Nm	1
-------------------------------------	----	---

Conductor section

AWG/kcmil conductor section

max 12

IEC

max mm<sup>2</sup> 1 or 2 / 2.5

Mounting adapter	LPXAU120
------------------	----------

Weight	g	16
--------	---	----

## Ambient conditions

## Temperature

Operating temperature

min °C -25


max °C +70

Storage temperature


min °C -40

max °C +85

## Dimensions



## Wiring diagrams



## Certifications and compliance

### Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

### Certificates

CCC

cULus

EAC

RINA

UL

## ETIM classification

ETIM 8.0

EC000204 -  
Lamp holder  
block for control  
circuit devices