



Product designation		Micro PLC - Base module
Product type designation		LRD12TD024
Auxiliary supply voltage		24VDC
Number of inputs	Nr.	6 digital + 2 digital/analog
Number of outputs	Nr.	4 transistor
Max I/O number		12 (8 inputs + 4 outputs) up to 36 with LRE modules

Power supply			
Rated auxil. supply voltage			24VDC
Operating voltage range			20.4...28.8VDC
Average current consumption	mA		125
Power consumption Max	W		4.5

Digital inputs			
Number of digital input	Nr.		6 + 2 digital/analog
Rated voltage	V		24VDC
Input signals		State 0 (OFF) State 1 (ON)	<5VDC >15VDC
Response time		0 to 1 (OFF-ON) 1 to 0 (ON-OFF)	4ms (0.5ms for high speed) 4ms (0.3ms for high speed)

Analog inputs			
Number of analog input	Nr.		2 digital/analog
Analog input type			Voltage inputs
Inputs signal range	V		0...10
Resolution			0.01V
Bit of conversion	bit		10
Current consumption at		10VDC	mA
			<0.17mA
Input impedance			kΩ
			>40
Admissible overload			VDC
			28
Sampling time			ms
			5...20ms(LADDER) 2...10ms (FBD)
Maximum cable length			m / ft
			≤30m/98ft (shielded wire)

Digital outputs			
Number of digital output	Nr.		4
type			Transistor

System resources			
------------------	--	--	--

Display	LCD display, 4 lines x 16 characters
---------	--------------------------------------

Connections

Terminals type	Screw
----------------	-------

Tightening torque for terminals	
---------------------------------	--

max	Nm	0.6
Max	lbft	0.4

Conductor section	
-------------------	--

AWG/Kcmil

min	26
max	14

IEC

min	mm ²	0.14
max	mm ²	2.5

Ambient conditions

Temperature	
-------------	--

Operating temperature

min	°C	-20
max	°C	+55

Storage temperature

min	°C	-40
max	°C	+70

Relative humidity	%	20...90% without condensation
-------------------	---	-------------------------------

Housing


Mounting	35mm DIN rail or screw fixing (M4x20mm)
----------	---

Degree of protection	IP20
----------------------	------


Dimensions (W x H x D)	mm	72 x 106 x 59.6
------------------------	----	-----------------

Weight	g	220
--------	---	-----

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 142
IEC/EN 61131-2
UL508

Certificates

cULus
EAC

ETIM classification

ETIM 8.0

EC001417 -
Logic module