





Product designation			Operator panel, 24VDC. RS232 and RS485 (Modbus-RTU Master) ports	
Product type designation			LRXP01	
Auxiliary supply voltage			24VDC	
Power supply				
Rated auxil. supply voltage			24VDC	
Operating voltage range			20.4...26.4VDC (-15%...+10%)	
Power consumption Max		W	1.9	
System resources				
Display			4.3" monochrome LCD display, green background + keypad with 24 keys	
Colors			monochrome, olivine background	
Resolution			192 x 64 pixel	
Touchscreen			No	
Communications				
Type of communication port			RS232 and RS485	
Connections				
Terminals type			Screw	
Tightening torque for terminals		max	Nm	1.8
		Max	lbft	10.4
Conductor section				
AWG/Kcmil		min	22	
		max	12	
IEC		min	mm²	0.4
		max	mm²	3.3
Ambient conditions				
Temperature				
Operating temperature		max	°C	+55
Storage temperature		min	°C	-40
		max	°C	+70

Relative humidity	%	10...95% without condensation
Maximum Pollution degree		2
Housing		
Degree of protection		IP65
Dimensions (W x H x D)	mm	179.5 x 101.5 x 33
Weight	g	200

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 142
IEC/EN 61131-2
UL508

Certificates

cULus
EAC

ETIM classification

ETIM 8.0

EC001412 -
Graphic panel