



Level control relay multifunction. Single voltage. Modular version LVM40 Multifunction: emptying and alarms, filling and alarms, emptying with priority start-up change, filling with priority start-up change, well draining and tank filling and alarms

Product designation

Product type designation

Function

#### Auxiliary supply

Supply voltage Type	Single voltage		
Rated auxiliary supply voltage $U_s$	AC		
	min	VAC	24
Operating voltage range	0.85...1.1 $U_s$		
Rated frequency	Hz		50/60
Power consumption Max	VA		4.5
Power dissipation Max	W		2.8

#### Output characteristics

Number of connectable electrodes	Nr.	5
Type of electrode	Electrode and electrode holders: SN1 / SCM / CGL / PS31 / PS3S or similar	
Electrode voltage	10 Vpp	
Sensitivity	k $\Omega$	2.5...200 adjustable

#### Time delay

Tripping time	s	1
Resetting time	s	1
Probe tripping delay	1...10s	

#### Relay outputs

Number of relays	Nr.	2
Relay state	Normally de-energised, energises at tripping	

Contact arrangement		1 changeover contact C/O-SPDT + 1 contact NO-SPST
Rated operational voltage AC (IEC)	VAC	250
Maximum switching voltage	VAC	400
IEC Conventional free air thermal current I <sub>th</sub>	A	8
UL/CSA and IEC/EN 60947-5-1 designation		B300
Electrical life (with rated load)	cycles	10 <sup>5</sup>
Mechanical life	cycles	30x10 <sup>6</sup>

#### Indications

Indication	1 green LED indicator for power on 2 red LEDs for relay state 2 red LEDs for probe state
------------	--

#### Functions

3 detecting electrodes (MIN, MAX and COM)	No
5 detecting electrodes (MIN1, MAX1, MIN2, MAX2 and COM)	Yes
Sensitivity adjustment 2.5...50k Ω	No
Sensitivity adjustment 2.5...100k Ω	No
Sensitivity adjustment 2.5...200k Ω	Yes
Adjustable sensitivity full-scale value 25-50-100-200 k Ω	Yes
Separate sensitivity adjustment for MAX probe (foam detection)	Yes
Emptying function	Yes
Filling function	Yes
Emptying function with MIN and/or MAX alarm	Yes
Filling function with MIN and/or MAX alarm	Yes
Emptying function with pump priority change	Yes
Filling function with pump priority change	Yes
Tank filling, well drawing and alarm	Yes
Filling-emptying adjustment selector	No
Programming selector for 5 different	Yes
Motor start-up priority change	No

#### Connections

Tightening torque for terminals	max	Nm	0.8
	max	Ibin	7
Conductor cross section			
AWG/Kcmil	min	AWG	24
	Max	AWG	12
IEC	min	mm <sup>2</sup>	0.2
	Max	mm <sup>2</sup>	4

#### Insulations

Rated insulation voltage U <sub>i</sub>	V	415
Rated impulse withstand voltage U <sub>imp</sub>	kV	6
Operating frequency withstand voltage	kV	4
Double insulation Supply / relay / electrode	VAC	≤250

#### Ambient conditions

Temperature

Operating temperature

min	°C	-20
max	°C	+60


Storage temperature

min	°C	-30
max	°C	+80


## Housing

Execution	Modular DIN rail mounting	
N° of modules	3	
Material	Self-extinguishing polyamide	
Mounting	35mm DIN rail (IEC/EN 60715) or by screws using extractable clips	
IEC degree of protection	IP40 on front / IP20 on terminals	
Dimensions (W x H x D)	mm	53.5 x 104.7 x 64.9
Weight	g	278

## Dimensions



## Wiring diagrams



## Certifications and compliance

### Compliance

CSA C22.2 n° 14

IEC/EN 60255-5

IEC/EN 61000-6-2

IEC/EN 61000-6-3

UL508

### Certificates

cULus

EAC

## ETIM classification

ETIM 8.0

EC001447 - (Fill)  
level monitoring  
relay