





Product designation	Direct-on-line starter		
Product type designation	M0P00912...5		
Electrical features			
Relay adj range	A	3-5	
IEC technical characteristics (≤440V)	Ie kW	A kW	5 1.5...2.2
Components			
Starter enclosure standard supplied	M0PA		
Contactor standard supplied	BG0910A		
Thermal relay standard supplied	RF95		
UL technical data			
Maximum UL/CSA horsepower ratings single-phase	220V-240V	HP	0.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole	200V-208V	HP	1
	220V-240V	HP	1
	440V-480V	HP	3
	550V-600V	HP	3
Mechanical features			
Weight	g		760
Ambient conditions			
Operating temperature	min max	°C °C	-25 +60
Storage temperature	min max	°C °C	-40 +70
Resistance & Protection			
Frontal IP degree	IP65		
Dimensions			



Wiring diagrams



I = Start; O = Stop/Reset

Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-1
UL508 CSA C22.2 n° 14

Certificates

CSAus
cULus
EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination