



Product designation  
Product type designation  
Motor type

Soft Starter  
ADXC  
Asynchronous  
three phase

### Electrical features

Supplies voltage

Type of system		Three phase
Rated supply voltage	V	220...400VAC
auxiliary supply voltage (Us)		110...400VAC
Rated frequency	Hz	50/60
Start command (Uc)		110...400VAC -15...+10%

Rated starter current Ie	A	37
--------------------------	---	----

Rated motor power

IEC ratings (T≤40°C)

230VAC	kW	9
400VAC	kW	18.5

UL ratings (T≤40°C)

220-240VAC	HP	10
380-415VAC	HP	20

Number of controlled phases	Nr.	2
Built-in bypass		Yes
Cooling System		Natural
Rated insulation voltage Ui	V	630

### Programming interface

Display	No
Programming with NFC technology	No
Optical port	No

### Startup and stop settings

Startup method		Voltage ramp with current limitation
Stop method		Voltage ramp or free-wheel stop
Acceleration ramp	s	1...20
Deceleration ramp	s	0...20
Startup voltage	%	0...85%

### Protections

Motor protection		Wrong phase sequence
------------------	--	-------------------------

### Ambient conditions

Temperature


Operating temperature

min	°C	-20
max	°C	+60°C (with derating >40°C)

Storage temperature

	min max	°C °C	-40 +80
Max altitude		m	1000
Relative humidity		%	<95 non condensing at 40°C
Pollution degree			2
Installation category			III
<b>Housing</b>			
Mounting			Screw-fixing or 35mm DIN rail
IP degree of protection			IP20
Dimensions (W x H x D)	mm		45 x 132 x 153.8
Weight	Kg		0.7

#### Dimensions



#### Certifications and compliance

##### Compliance

CSA C22-2 n° 14  
IEC/EN 60947-1  
IEC/EN 60947-4-2  
UL508

##### Certificates

cULus  
EAC  
RCM

#### ETIM classification

ETIM 8.0

EC000640 - Soft  
starter